







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压: 30V, AC/DC。
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega \text{ min.}$
6. 额定电流: 0.5A, AC/DC
(使用 AWG #32, $0.0038 \pm 0.002\text{mm}$)。
7. 耐压: AC 200V/1分钟。



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
序号	品名		材质	
1	0.8-C型WTB 刺破型公头胶芯		PA66加玻纤 UL94 V-0 米黄色	
2	0.8-C型WTB 刺破型公头端子		铜合金/镀金	

Part No	CKT	A	B	C	D
C-0.8-1-Y2P42	2	0.80	1.78	2.18	2.40
C-0.8-1-Y3P42	3	1.60	2.58	2.98	3.20
C-0.8-1-Y4P42	4	2.40	3.38	3.78	4.00
C-0.8-1-Y5P42	5	3.20	4.18	4.58	4.80
C-0.8-1-Y6P42	6	4.00	4.98	5.38	5.60
C-0.8-1-Y7P42	7	4.80	5.78	6.18	6.40
C-0.8-1-Y8P42	8	5.60	6.58	6.98	7.20
C-0.8-1-Y9P42	9	6.40	7.38	7.78	8.00
C-0.8-1-Y10P42	10	7.20	8.18	8.58	8.80
C-0.8-1-Y11P42	11	8.00	8.98	9.38	9.60
C-0.8-1-Y12P42	12	8.80	9.78	10.18	10.40
C-0.8-1-Y13P42	13	9.60	10.58	10.98	11.20
C-0.8-1-Y14P42	14	10.40	11.38	11.78	12.00
C-0.8-1-Y15P42	15	11.20	12.18	12.58	12.80
C-0.8-1-Y16P42	16	12.00	12.98	13.38	13.60
C-0.8-1-Y17P42	17	12.80	13.78	14.18	14.40
C-0.8-1-Y18P42	18	13.60	14.58	14.98	15.20
C-0.8-1-Y19P42	19	14.40	15.38	15.78	16.00
C-0.8-1-Y20P42	20	15.20	16.18	16.58	16.80

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. C-0.8-1-YNP42	TITLE: 0.80 Pitch C型WTB刺破公头		
X.X±0.20			MANUFACTURE DWG		
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	 SCALE SHEET		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			