





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		pin数表尺寸补充, 图面升级整理图面	2024.08.19	阿树



Poles	DIM	
	A	B
02	2.54	5.08
03	5.08	7.62
04	7.62	10.16
05	10.16	12.70
06	12.70	15.24
07	15.24	17.78
08	17.78	20.32
09	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48

X9254WV-06-N0SN	Nylon66	Tin Plated	X9254H
PART NO	Material	Material(Brass)	Suitable XKB Housing

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKLB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.54mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X9254WV-06-N0SN		
APPROVED		SIZE: A4	DWG NO.: X-X9254WV-06-N0SN		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1/1	REVISION A1