

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.17	阿树

Specifications :


Voltage rating: 150V AC / DC
Current rating: 0.5A AC / DC
Withstanding voltage: 250V AC/minute
Temperature range: -45°C~+125°C
Insulation resistance: ≥500MΩ
Contact resistance: ≤50mΩ
After environmental testing: ≤60mΩ
Max.Processing Temp: 230°C for 30~60 seconds
(260°C for 10 seconds)

PART NO.:

X1016 W F-41 B-46 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
② Category: W-wafer
③ Welding Board Angle: F-Female
④ Row No.-Pin No.: XX-09P~51P
⑤ B-Positioning column without positioning plate
⑥ Material: 46-PA46 94V-0;
6T-PA6T 94V-0;
⑦ Planting Category: SN-Bright tin plating;

poles	Dimensions(mm)				
	A	B	C	D	E
09	8.30	3.00	4.00	7.10	
11	9.30	4.00	5.00	8.10	
13	10.30	5.00	6.00	9.10	
15	11.30	6.00	7.00	10.10	
17	12.30	7.00	8.00	11.10	
19	13.30	8.00	9.00	12.10	
21	14.30	9.00	10.00	13.10	5.00
23	15.30	10.00	11.00	14.10	6.00
25	16.30	11.00	12.00	15.10	7.00
31	19.30	14.00	15.00	18.10	10.00
41	24.30	19.00	20.00	23.10	15.00
51	29.30	24.00	25.00	28.10	20.00



X1016WF-41B-46SN	Nylon 46 UL 94V-0	Phosphor Bronze	Tin-Plated	Brass	Tin-Plated
X1016WF-41B-6TSN	Nylon 6T UL 94V-0				
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tab)	Finish (Solder Tab)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.00 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1016WF-41B-46SN
APPROVED		SIZE: A4	DWG NO.: X-X1016WF-41B-46SN