

HSF



RoHS

SPECIFICATION

Current Rating: 1.5Amp
Insulation Resistance: 1000M ohms min
Contact Resistance: 20M ohms max
Dielectric Withstanding: AC500V
Operating Temperature: -65°C to +125°C
Contact Material: Brass
Insulator Material: PA6T,UL 94V-0 Black

Ordering Code:

PC104D02- X - X - D - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦

① Series No:

② No. of Contacts
02 To 80

③ Contact Plating:

G0:Gold flash S0:Selective
G1:3U" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin

④ Connector Type
D: Dual⑤ Terminal Type
H: A~D





Please mark the desired length in the H

⑥ Insulator Material

A: PBT
B: PA6T
C: LCP
D: PA46
E: PA9T

⑦ Packing

A: Tray
B: Bag
T: Tube
U: Tube+CAP
R: Tape&Reel
W: Tape&Reel+CAP



PCB LAYOUT

Terminal Type	H	B
TYPE A	8.35	13.1
TYPE B	8.35	3.4
TYPE C	9.35	2.28
TYPE D	9.70	11.9

Unless Otherwise specified tolerance

X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE:

As Shown

UNIT:

mm

DRAW

YG ZHONG

DATE


01/05/2016

CHECK

BobYang

DATE

01/05/2016



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE: 2.00mm Female Header Dual Row
Straight Type Add Housing

DRAWING NO: PC104D02-XXDXXX

PRODUCT NO: PC104D02-XXDXXX



REV

Flip the additional housing

05/10/2023

DESCRIPTION

DATE