




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.19	阿树

Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating pin Ø:0.60mm
Contact resistance:max 10mΩ
Dielectric strength:min 1000V RMS
Operating temperature:-40°C~+105°C
Soldering temperature:+255°C

PART NO.:
X5511 W V-01 -C396 D43-1220
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Straight 180°
- ④Row No-Pin No:XX-01P-XXP
- ⑤Pin Length :C=3.96mm
- ⑥Pin Length :D=4.3mm
- ⑦1220:Type1220

Recommended P.C.B Layout(±0.05)

X5511WV-01-C396D43-1220	PPS 94V-0	Brass	Tin Gold 1u''	X5511F
PART NO	Material	Material(Pin)	Finish(Terminal)	Mates With XKB Pin Header

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCE	
AuCES	



DESIGN	阿树	VIEW:	30°	MODEL TYPE:	2.54mm BTB Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X5511WV-01-C396D43-1220
APPROVED		SIZE:	A4	DWG NO.:	X-X5511WV-01-C396D43-1220
		SCALE	PAGE	REVISION	
		N/A	1/1	A1	