




LEFT SIDE VIEW




FRONT VIEW




BOTTOM VIEW




RIGHT SIDE VIEW



RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE




TOP VIEW




BACK VIEW

ELECTRICAL 电气:

1. Turn ratio 匝数比:1~2:J1~J2=1CT:1CT(±2%)
3~6:J3~J6=1CT:1CT(±2%)
2. OCL 已占搭载量:350uH Min at 100KHz 100mV 8mA DC.
3. Insertion Loss 插入损耗: -1.0 dB Max 1~100MHz
4. Return loss 回程损耗: -18dB Min 1~30MHz
-14dB Min 30~60MHz
-10dB Min 60~100MHz
5. Cross talk 声道串扰: -40dB Min 1~30MHz;
-35dB Min 30~60MHz;
-30dB Min 60~100MHz;
6. CMR 共模抑制: -30dB Min 1~100MHz;
7. Hi-Pot 耐压测试: 1500V AC & 2250V DC 6S
1mA PRI TO SEC



LED Specification



Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Green	568nm	20mA	1.85-2.45V
Yellow	585nm	20mA	1.7-2.2V

XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: PBT,UL94V-0,BLACK.

TERMINALS BRACKET 端子支架: PBT,UL94V-0,BLACK.

SHIELD 保护物: C2680,T=0.20MM,NICKEL PLATING ON ALL AREA.

TERMINAL 端子: PHOSPHOR BRONZE C5210,T=0.35MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.

MATING FORCE 配合力: 23N MAX.

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 儲存溫度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "*"

DSND		SCALE: N/A	MODEL TYPE: RJ JACK		
DWN		VIEW: 	PART NO.:		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4	X01AB002FA2AD		
PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0

XKIE

XKB INDUSTRIAL PRECISION CO.,LIMITED