

1

2



3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.16	阿 树

2.60 [0.102]

Circuit 1



■SPECIFICATIONS




- Voltage rating:250V AC/DC
- Current rating:5A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing: ≤20mΩ

PART NO.:

X3025 W R-08 C-LP SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No
- ② Category:W-Wafer
- ③ Welding Board Angle:R-Stright 90°
- ④ Row No-Pin No: XX-01P~12P
- ⑤ Plug the Pin & Special No:C-The harpoon
- ⑥ Material:LP-LCP UL94V-0
66-PA66 94V-0
- ⑦ Planting Category:SN-Bright tin plating
- ⑧ Color:Blank-natural color Black



P.C.B.LAYOUT

General Tole rance±0.05

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
01	---	6.65	07	18.00	24.65
02	3.00	9.65	08	21.00	27.65
03	6.00	12.65	09	24.00	30.65
04	9.00	15.65	10	27.00	33.65
05	12.00	18.65	11	30.00	36.65
06	15.00	21.65	12	33.00	39.65

X3025WR-08C-66SN	PA66 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WR-08C-LPSN	LCP UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树	VIEW:		MODEL TYPE:	
CHECKED		UNIT: mm/in		PART NO.:	
APPROVED		SIZE: A4		DWG NO.:	
				X-X3025WR-08C-LPSN	
SCALE		PAGE	REVISION		
N/A		1/1	A1		

1

2

3

4