


NO.	ECN NO.	DESCRIPTION	DATE

客户图



Note:
1: Material (材料):
Barrel: Brass C6801 (针管: 无铅铜 C6801)
Plunger: Brass C6801 (针头: 无铅铜 C6801)
Spring: SUS304 (弹簧: SUS304)

2: Plating (电镀):

Barrel: 5u' Au over 200u' Cu over 200u' Ni (针管: 镀金5u', 铜底200u', 镍底200u')
Plunger: 5u' Au over 200u' Cu over 200u' Ni (针头: 镀金5u', 铜底200u', 镍底200u')

Spring: Gold plated (弹簧: 镀金)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V; 2A (额定电压&电流: 直流12V, 2A)
Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical (机械性能):

Force: 80g±20% at working height. (80g±20% 在工作高度)。
Durability: 10,000 cycles (min) (寿命: 10000次)

5: WorkTemperature (工作环境):

Withstanding Higt Temperature: 280℃
Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司			
HTTP://WWW.XYZ060PIN.COM			
TEL:0755-28773277 FAX:0755-28891353			
			
SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2024.7.27	D.O	
THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±1.00°
X.X	±0.10mm	X.X	±2.00°
X.	±0.20mm	X.	
DESIGNED BY:		DWG. NO.	
CHECKED BY:		YZP0799-30077-02	
APPROVED BY:		TITLE:	
		Pogo pin 连接器	



深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL: 0755-28773277 FAX: 0755-28891353