





Specifications :

- Voltage rating: 50 V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 100M\Omega$
- Contact resistance: $\leq 20m\Omega$



X1011 WRS-2x25-9T XX
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Right 90°
- ④ Welding Way:S-SMT
- ⑤ Row No.Pin No.2*02-2*25
- ⑥ Material:9T-PA9T 94V-0
- ⑦ Planting Category:SN-Bright tin plating
V01-All Gold Flash



Poles	Dimensuons(mm)		
	A	B	C
2*05	4.00	8.10	5.5
2*06	5.00	9.10	6.5
2*08	7.00	11.10	8.5
2*10	9.00	13.10	10.5
2*15	14.00	18.10	15.5
2*20	19.00	23.10	20.5
2*25	24.00	28.1	25.5

X1011WRS-2x25-9TV01	PA9T UL 94V-0	Phosphor Bronze	Gold-Flash	X1011H
X1011WRS-2x25-9TSN	PA9T UL 94V-0	Phosphor Bronze	TIN-Plated	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

DSND		SCALE: N/A	MODEL TYPE: 1.0mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X1011WRS-2x25-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X1011WRS-2x25-9TV01
APPD		SIZE: A4	
PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1/1
			A0

XKB INDUSTRIAL PRECISION CO.,LIMITED