



NST022C65K SiC Power MOSFET

1 Features and Benefits

- High Blocking Voltage with Low On-Resistance
- High Speed Switching with Low Capacitances
- Easy to Parallel and Simple to Drive
- Avalanche Ruggedness
- Halogen Free, RoHS Compliant
- Higher System Efficiency
- Reduced Cooling Requirements
- Increased Power Density
- Increased System Switching Frequency

2 Application

- Motor driver
- Solar Inverters
- Switch Mode Power Supplies
- High Voltage DC/DC Converters
- Battery Chargers
- Motor Drives
- Pulsed Power applications


3 Description

NST022C65K is a 650V SiC MOSFET that contributes to miniaturization and low power consumption of applications. By leveraging advanced SiC technology, it delivers a superior balance between conduction efficiency and switching speed.


Device information

Part Number	Package	Device Marking
NST022C65K	TO-252	NST022C65K

TO252 Pin Configuration



Schematic Diagram



Pin Assignment

4 Selection Guide

Part Number	TYPE	R _{DS_(ON)}	VDS	VTH
NST022C65K	N	215mΩ	650V	3.4V

5 Ordering Guide

Part Number	LOGO	Package
NST022C65K	 NST022C65K XXXXXX	TO-252

6 Revision history

Version	Content	Time
V1.0	Create	2024.02.13



TABLE OF CONTENTS

1 FEATURES AND BENEFITS	1
2 APPLICATION	1
3 DESCRIPTION	1
4 SELECTION GUIDE	2
5 ORDERING GUIDE	2
6 REVISION HISTORY	2
7 FUNCTION PIN DESCRIPTION	4
8 PRODUCT SPECIFICATIONS	5
9 PACKAGE INFORMATION	6
10 ATTENTION	7

7 Function Pin Description




Figure7-1 3-Pin TO252 Top view

Table7-1 Lead Definitions

Symbol	Description
G	GATE
D	DRAIN
S	SOURCE

8 Product specifications

8.1 Absolute Maximum Ratings

PARAMETER	SYMBOL	MAX	UNIT
Drain-Source Voltage	V_{DS}	650	V
Gate-Source Voltage	V_{GS}	-10/+22	V
Drain Current-Continuous	$I_D(T_C=25^{\circ}C)$	15.4	A
	$I_D(T_C=100^{\circ}C)$	10.9	
Drain Current-Pulsed	I_{DM}	24.5	A
Maximum Power Dissipation	P_D	55	W
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 To 175	$^{\circ}C$

8.2 Thermal Characteristic

PARAMETER	SYMBOL	MAX	UNIT
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	2.7	$^{\circ}C/W$

8.3 Electrical Characteristics (TA=25°C unless otherwise noted)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D = 100μA	650	--	--	V
Gate-Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 3.5mA, T _J =25℃	2.7	3.4	4.1	V
		V _{DS} = V _{GS} , I _D = 3.5mA, T _J =175℃	--	2.4	--	V
Gate-Body Leakage	I _{GSS+}	V _{DS} = 0V, V _{GS} = +22V	--	--	250	nA
Gate-Body Leakage	I _{GSS-}	V _{DS} = 0V, V _{GS} = -10V	--	--	-250	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 650V, V _{GS} = 0V, T _J =25℃	--	0.1	100	μA
		V _{DS} = 650V, V _{GS} = 0V, T _J =175℃	--	1	--	
Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} = 15V, I _D = 8A, T _J =25℃	--	215	280	mΩ
		V _{GS} = 15V, I _D = 8A, T _J =175℃	--	229	--	
		V _{GS} = 18V, I _D = 8A, T _J =25℃	--	163	--	
		V _{GS} = 18V, I _D = 8A, T _J =175℃	--	207	--	
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{DS} = 400V, V _{GS} = 0V, f = 1MHz	--	289	--	pF
Output Capacitance	C _{oss}		--	23	--	
Reverse Transfer Capacitance	C _{rss}		--	2.1	--	
Switching Capacitance						
Turn-On Delay Time	t _{d(on)}	V _{DD} = 400V, I _D = 8A V _{GS} = 15V, R _G = 20Ω	--	35	--	ns
Turn-On Rise Time	t _r		--	30	--	
Turn-Off Delay Time	t _{d(off)}		--	40	--	
Turn-Off Fall Time	t _f		--	50	--	
Total Gate Charge	Q _g	V _{DS} = 400V, I _D =8A, V _{GS} =15V	--	12.5	--	nC
Gate-Source Charge	Q _{gs}		--	4.5	--	
Gate-Drain Charge	Q _{gd}		--	1.5	--	
Drain-Source Diode Characteristics						
Diode Forward Voltage	V _{SD}	V _{GS} = 0V, I _{SD} = 4A, T _J =25℃	--	3.6	--	V
		V _{GS} = 0V, I _{SD} = 4A, T _J =175℃	--	3.2	--	V

9 Package Information

TO-252 Package Information

SYMBOL	MILLIMETER			SYMBOL	MILLIMETER		
	MIN(mm)	TYP(mm)	MAX(mm)		MIN(mm)	NOM(mm)	MAX(mm)
A1	0.00	—	0.10	E	9.90	10.10	10.30
A2	2.20	2.30	2.40	E1	6.00	6.10	6.20
A3	1.02	1.07	1.12	E2	5.30REF		
b	0.65		0.77	e	2.286BSC		
b1	0.64	0.69	0.74	L	1.40	1.50	1.60
C	0.51	—	0.55	L2	0.90	—	1.25
c1	0.50	0.51	0.52	L3	0.60	0.80	1.00
D	6.50	6.60	6.70	L4	1.70	1.80	1.90
D1	5.33REF			Θ	0		8°
D2	4.83REF						

TO-252 Package Outlines





10 ATTENTION

- The NST022C65K product and its associated datasheet (hereinafter referred to as the "Product") provided by our company (NSIC Technology (Wuxi) Co., Ltd.) are not designed or tested for applications requiring very high reliability. Examples include life support systems, aircraft control systems, or other applications where failure could result in serious personal injury and/or material damage. Before using this product in this application, be sure to check with a representative of the company near you.
- The Company shall not be liable for equipment failure resulting from instantaneous or continuous use outside of product specifications, including but not limited to maximum ratings, range of operating conditions, or other parameters. The user shall ensure that all prescribed specifications and conditions are observed in the use of this product.
- The performance, characteristics and functions of the product described in this datasheet are based on the test results of the product in an independent state, and do not constitute a guarantee of the performance, characteristics and functions of the product after installation in the user's product or equipment. For symptoms and conditions that cannot be evaluated in a product-independent state, users should always install and test the product in their product or equipment for verification.
- Although we are committed to providing high quality, high reliability products, all semiconductor products have a certain probability of failure. This probabilistic failure may result in an accident or event that endangers personal safety, causes fire or smoke, or causes other property damage. Therefore, when designing equipment, users should take safety measures to prevent such accidents or incidents. These measures include, but are not limited to, safety design, protection and error prevention circuits, redundancy design, and structural design.
- If any product or technical data described in this datasheet is subject to local export control laws and regulations, such product shall not be exported until an export license has been issued by the relevant authorities in accordance with such laws.
- This datasheet and the information it contains, including circuit diagrams and circuit parameters, are for example purposes only and are not guaranteed for mass production. The information in this datasheet is believed by the Company to be accurate and reliable, but the Company makes no warranty, express or implied, as to its use or any infringement of the intellectual property or other rights of third parties.
- This datasheet and the information described herein are subject to change without prior notice due to product/ technical improvements, etc. When designing the equipment, please refer to the "delivery specifications" of the silicon products you intend to use.
- This statement is based on information as of February 2024 and is subject to change without notice.