

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.8	阿树

A

B

C



D

A

B

C

D



- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance: $\geq 1000M\Omega$
 - Contact resistance: $\leq 20m\Omega$
 - After environmental testing: $\leq 30m\Omega$

PART NO.:

X9555 W R-2x16 E-PT SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:2xXX-02~20Pin
⑤Special NO: E-matching 9555H-2xXXE HSG,
K the feet, DIP=2.90mm 1-K the feet,DIP=2.50mm
⑥Material:PT-PBT 94V-0
⑦Plating Category: SN-Bright Tin Plating 70u"
V01-Gold Flash

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	5.09	10.12	8.12	2x12	27.94	32.98	30.98
2x04	7.62	12.66	10.66	2x13	30.48	35.52	33.52
2x05	10.16	15.20	13.20	2x14	33.02	38.06	36.06
2x06	12.70	17.74	15.74	2x15	35.56	40.60	38.60
2x07	15.24	20.28	18.28	2x16	38.10	43.14	41.14
2x08	17.78	22.82	20.82	2x17	40.64	45.68	43.68
2x09	20.32	25.36	23.36	2x18	43.18	48.22	46.22
2x10	22.86	27.90	25.90	2x19	45.72	50.76	48.76
2x11	25.40	30.44	28.44	2x20	48.26	53.30	51.30

Dim"L"	E1	2.50
	E	2.90

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树
UNIT: mm/in
SIZE: A4

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
2.54mm Crimp Style Connectors
PART NO.:
X9555WR-2x16E-PTSN
DWG NO.: