






客户图



Note:

1: Material (材料):

Housing: PA46+30%GF (胶芯: PA46)

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating (电镀):

Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

Insulation Resistance: 1,000M Ω minimum. (绝缘电阻: 1,000M Ω 以上)

Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)

4: Mechanical (机械性能):

Force: 40g $\pm$ 20% at working height. (40g $\pm$ 20% 在工作高度)。

Durability: 10,000 cycles (min) (寿命: 10000次)

5: Work Temperature (工作环境):

Withstanding Higt Temperature: 280 $^{\circ}$ C

Operational Temperature: -20 $^{\circ}$ C~ +70 $^{\circ}$ C

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:

N/A

UNIT

mm

SHEET:

1 of 1

PROJECTION



DATE:

2023.7.26

VER.

D.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH

ANGLE

X.XX $\pm$ 0.05mm

X.X $\pm$ 0.10mm

X. $\pm$ 0.20mm

X.XX $\pm$ 0.50 $^{\circ}$

X.X $\pm$ 1.00 $^{\circ}$

X. $\pm$ 2.00 $^{\circ}$

DESIGNED BY:

CHECKED BY:

APPROVED BY:

DWG. NO.

TITLE:

YZR0185-17070-06040-01

Pogo pin 连接器