


1.Features

- TRANSISTOR (PNP)
- For Switching and AF Amplifier Applications
- Ideally suited for automatic insertion

2.Pinning Information

Pin	Symbol	Description
1	B	BASE
2	E	EMITTER
3	C	COLLECTOR

SOT-323



3.Absolute Maximum Ratings $T_A = 25^\circ\text{C}$

Parameter	Symbol	Value	Units
Collector-Base Voltage	V_{CBO}	-50	V
Collector-Emitter Voltage	V_{CEO}	-45	V
Emitter-Base Voltage	V_{EBO}	-5	V
Collector Current –Continuous	I_C	-0.1	A
Collector Power Dissipation	P_C	150	mW
Thermal Resistance From Junction To Ambient	$R_{\theta JA}$	833	$^\circ\text{C/W}$
Operation Junction and Storage Temperature Range	T_J, T_{STG}	55 to 150	$^\circ\text{C}$




4. Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Conditions	Min	Max	Units
Collector-base breakdown voltage	V_{CBO}	$I_C = -10\mu\text{A}$, $I_E = 0$	-50		V
Collector-emitter breakdown voltage	V_{CEO}	$I_C = -10\text{mA}$, $I_B = 0$	-45		V
Emitter-base breakdown voltage	V_{EBO}	$I_E = -1\mu\text{A}$, $I_C = 0$	-5		V
Collector Cutoff Current	I_{CBO}	$V_{CB} = -30\text{V}$, $I_E = 0$		-15	nA
DC current gain	h_{FE}	$V_{CE} = -5\text{V}$, $I_C = -2\text{mA}$	220	475	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = -100\text{mA}$, $I_B = -5\text{mA}$		-0.65	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C = -100\text{mA}$, $I_B = -5\text{mA}$		-1.1	V
Transition frequency	f_T	$V_{CE} = -5\text{V}$, $I_C = -10\text{mA}$, $f = 100\text{MHz}$	100		MHz
Collector output capacitance	C_{ob}	$V_{CB} = -10\text{V}$, $f = 1\text{MHz}$		4.5	pF




5. Typical Characteristic





6.SOT-323 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	b _p	c	D	E	e	e1	H	L _p	Q
Min	0.8	0.1	0.3	0.10	1.8	1.15	1.3	0.65	2.0	0.15	0.13
Max	1.1		0.4	0.25	2.2	1.35			2.2	0.45	0.23



7.Ordering Information



Order Code	Package	Base QTY	Delivery Mode
UMW BC857BW	SOT-323	3000	Tape and reel



8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.