


客户图

NO.	ECN NO.	DESCRIPTION	DATE
1	A.1	A. 1-6. 8±0.15改为6. 5±0.15	2020. 8. 10
2	A.1	A. 1-5. 8工作高度变为5. 5	2020. 8. 10



Note:

1: Material(材料):

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀):

Barrel: 5u' Au over 50~80u' Ni (针管: 镀金5u', 镍底50~80u'.)

Plunger: 5u' Au over 50~80u' Ni (针头: 镀金5u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性):

Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V, 1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能):

Force: $20g \pm 5g$ at working height. ($20g \pm 5g$ 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture(工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$

6: Salt spray test(盐雾测试): 根据EIA-364-26, 测试条件: 5%盐水保持48小时。无氧化, 腐蚀, 生锈等不良现象。

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZP0332-17075-01
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo pin 连接器
DATE:	2020.08.17	VER.	A.1	X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^{\circ}$	APPROVED BY:			
				X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^{\circ}$				
				X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^{\circ}$				