

SOT-523 Plastic-Encapsulate Transistors


Features

- Power dissipation of 200mW

Mechanical Data

- Case: SOT-523
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Collector-Emitter Voltage

V_{CEO} -25V

Collector Current

-0.5 Ampere



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-523	R1	0.0025	3000	45000	180000	7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Collector-Base Voltage	V _{CBO}	V	-40
Collector-Emitter Voltage	V _{CEO}		-25
Emitter-Base Voltage	V _{EBO}		-5
Collector Current	I _C	A	-0.5
Collector Power Dissipation	P _C	mW	200
Storage temperature	T _{stg}	°C	-55 ~+150
Junction temperature	T _j	°C	-55 ~+150

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Type	Max
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	V	$I_C=-100\mu A, I_E=0$	-40	—	—
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$		$I_C=-1mA, I_B=0$	-25	—	—
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$		$I_E=-100\mu A, I_C=0$	-5	—	—
Collector cut-off current	I_{CBO}	nA	$V_{CB}=-40V, I_E=0$	—	—	-100
Collector cut-off current	I_{CEO}		$V_{CB}=-20V, I_B=0$	—	—	-100
Emitter-Base cut-off current	I_{EBO}		$V_{EB}=-3V, I_C=0$	—	—	-100
DC current gain	$h_{FE(1)}$	—	$I_C=-50mA, V_{CE}=-1V$	120	400	—
	$h_{FE(2)}$		$I_C=-500mA, V_{CE}=-1V$	50	—	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	V	$I_C=-500mA, I_B=-50mA$	—	—	-0.6
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	V	$I_C=-500mA, I_B=-50mA$	—	—	-1.2







CLASSIFICATION OF hFE

ITEM	L	H	J
Range	120-200	200-350	300-400

Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	TYP	Max
Transition frequency	f_T	$I_C=-20mA, V_{CE}=-6V, f=30MHz$	MHz	—	150	—

● **Ratings And Characteristics Curves** ($T_a=25^\circ\text{C}$ Unless otherwise specified)



Package Outline Dimensions (SOT-523)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.65	0.85	0.026	0.033
A1	0.40	0.60	0.016	0.024
B	0.25	0.35	0.010	0.014
b	0.15	0.25	0.006	0.010
C	0.05	0.15	0.002	0.006
D	0.70	0.90	0.028	0.035
D1	1.50	1.70	0.059	0.067
E	1.5	1.7	0.059	0.067
e	0.95	1.05	0.037	0.041
H	-	0.10	-	0.004
L	0.17	-	0.007	-

Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.50	0.70	0.020	0.028
B	0.60	0.80	0.024	0.031
C	0.90	1.10	0.035	0.043
D	1.20	1.40	0.047	0.055