


PART NO 料号	SLT068125H100MNB	DESCRIPTION 产品名称	RADIAL TYPE CHOKE COILS 卧式电感
---------------	------------------	---------------------	---------------------------------

1、HAPE&DIMENSION(UNIT:m/m)

外观图形尺寸(单位:m/m)



A	23.5MAX.
B	11.5MAX.
C	10±2
D	1.2±0.1
F	1.5MAX


2、 ELECTRICAL SCHEMATICS 电路原理图

(1) INDUCTANCE :AT: 1KHZ 0.3V (TH2816B) (30Ω)

L(1-2):10uH±20%

(2) DC RESISTANCE : AT: 25 °C

DCR(1-2): 10mΩMAX



3、 Material List:材料清单

NO.	Items	Material	Suppliers	UL.NO
1	Core	068125	SHANDONG HUIJIA ELECTRONICS CORPORATION OR EQUIVALENT	
2	Wire	2UEW-B	HONGQI OR YIDA ELECTRIC WIRE	E344055
3	TIN	环保高温锡条	YUEXING	

4、ELECTRICAL CHARACTERISTIC:电气特性

MEAS.ITEM 测试项目	L (1-2)	DCR (1-2)
	1KHz 0.3V	25℃
SPEC 电性范围	10uH ±20%	10mΩ MAX
01	9.80	4.10
02	9.90	4.20
03	10.10	4.21
04	10.20	4.18
05	10.50	4.18
X	10.10	4.17
σ	0.245	0.039
1. TEST INSTRUMENTS: ☐ HP-4284A METER ☐ HP-4285A METER ☐ HP-4191A METER ☐ CH-3200 METER ☐ CH-310 METER ☐ CH-3305 METER ☒ VR113+VR712 METER ☒ WK3260B+3265B METER ☐ VR562 METER ☒ CH-502B DCR METER 2.CONDITION: TEMPERATURE: 25℃		