



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X1	产品尺寸变更，图面升级整理图面	2025.03.11	阿树



PART NO.:

X9357 W R-2x10-N2 SN
① ② ③ ④ ⑤ ⑥

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No.Pin No:2xXX-2x01~2x12Pin
- ⑤Material:N0-PA66 94V-0; N2-PA66 94V-7 LP-LCP94V-0;
- ⑥Planting Category:V:All Gold-Plated*01-Gold Flash; SN-Bright tin plating 70u"

Poles	Dimensions(mm)	
	A	B
2x01	---	5.60
2x02	4.20	9.80
2x03	8.40	14.00
2x04	12.60	18.20
2x05	16.80	22.40
2x06	21.00	26.60
2x07	25.20	30.80
2x08	29.40	35.00
2x09	33.60	39.20
2x10	37.80	43.40
2x11	42.00	47.60
2x12	46.20	51.80

- SPECIFICATIONS
- Voltage rating:600V AC/DC
 - Current rating:9A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-45°C+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

X9357WR-2x10-N0V01	Nylon 66 UL 94V-0; White	Brass	Gold-Flash	X9357H	1,000Pcs
X9357WR-2x10-N0SN	Nylon 66 UL 94V-0		Tin-Plated		
X9357WR-2x10-N2V01	Nylon 66 UL 94V-2; White semi transparent		Gold-Flash		
X9357WR-2x10-N2SN	Nylon 66 UL 94V-2		Tin-Plated		
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB	Q'ty/Bag

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	UNIT: mm/in
CHECKED		SIZE: A4	
APPROVED			

MODEL TYPE:	4.20 mm Crimp Style Connectors
PART NO.:	X9357WR-2x10-N2SN
DWG NO.:	X-X9357WR-2x10-N2SN