


RO

- ▶ 3.2*2.5*0.95mm 4Pin 小体积
- ▶ 抗冲击振动、快速起振低至 1ms
- ▶ 可兼容多个电压(1.8-3.3V)，低功耗
- ▶ 符合 RoHS、Reach 认证标准，绿色环保



技术参数 Technical Parameter

输出模式	Output Type	CMOS
输出负载	Output Load	15PF
振荡模式	Ocsillation Mode	Fundamental
消耗电压	Supply Voltage	1.8V,2.5V,2.8V,3.3V,5.0V
频率范围	Frequency Range	1MHz ~ 125MHz / 32.768KHz
频率偏差	Frequency Stability	±25ppm,±50ppm,or specify
工作温度范围	Operating Temperature Range	-40 ~ +85℃, -40 ~ +125℃
储存温度范围	Storage Temperature Range	-55+125℃
输入电压	Voltage Vol(Max) / Voh(Min)	0.1VDD / 0.9VDD
上升/下降时间	Rise(Tr Max) / Fall(Tf Max)Time	8ns MAX
消耗电流	Supply Current	20mA MAX
占空比	Symmetry	40 ~ 60%
起始时间	Start-Up Time	5ms MAX
相位抖动	Phase Jitter(12khz ~ 20mhz)	1ps MAX
老化率	Aging(At25℃)	±3ppm / year MAX

外观尺寸 Dimension(Unit:mm)

