






2Pin
PCB REFERENCE DIAGRAM
TOLERANCE:±0.05



04-12Pin
PCB REFERENCE DIAGRAM
TOLERANCE:±0.05

G-Switch Specification:

- 1.Current rated: 23A AC/DC
- 2.Voltage rating: 600V AC/DC
- 3.Withstanding voltage: 2200V AC
- 4.Contact resistance: 10mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 30Cycles
- 7.Removal force: 1.0kgf/Pin min
- 8.Operating temperature range: -40°C ~ +105°C



GT-A5701 W V D-2 XX X XX 01

G-Switch

Series No

Connector
W-Wafer

Angle
V-180°

Termipoint
D-DIP

Terminal Plating
MT-Matte Tin

Housing Colour
B-Black

Pin Q' PY
02~12

Row NO
2-Dual Dows

Ordering Information:

Circuit	Dimensions(mm)		Circuit	Dimensions(mm)	
	A	B		A	B
02	--	8.35	08	17.10	23.45
04	--	12.05	10	22.80	29.15
06	11.40	17.75	12	28.50	34.85

2	PIN MATERIAL	High Conductivity Copper Alloy	MATTE Tin
1	HOUSING	LCP,94V-0	BLACK
NO.	PART NAME	MATERIAL	REMARK



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X ±0.40
X.x ±0.30
X.xx ±0.20
X* ±5°
X.x° ±3°

Title: Wafer 5.70mm Pitch MX 180° DIP
With Lock Type Dual Dows Connector

Molde Code: GT-A5701WVD-2XXXXX01

DRAWN	CHECKED	APPROVED	DATE
Hu	Hu	Chen	2021.10.20

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/2

1

2

3

4

5

A

A

B

B

C


C

D


D

E


E




2Pin




4Pin




6Pin




8Pin



10Pin



12Pin



GT-A5701 W V D-2 XX X XX 01

G-Switch

Series No

Connector
W-WaferAngle
V-180°Termipoint
D-DIPTerminal Plating
MT-Matte TinHousing Colour
B-BlackPin Q' PY
02~12Row NO
2-Dual Dows**G-Switch Specification:**

- 1.Current rated: 23A AC/DC
- 2.Voltage rating: 600V AC/DC
- 3.Withstanding voltage: 2200V AC
- 4.Contact resistance: 10mΩ max.
- 5.Insulation resistance: 1000MΩ min
- 6.Durability cycle: 30Cycles
- 7.Removal force: 1.0kgf/Pin min
- 8.Operating temperature range: -40°C ~ +105°C

Ordering Information:

Circuit	Dimensions(mm)		Circuit	Dimensions(mm)	
	A	B		A	B
02	--	8.35	08	17.10	23.45
04	--	12.05	10	22.80	29.15
06	11.40	17.75	12	28.50	34.85

SCALE: 1:1 UNIT: mm
SIZE: A4Unless otherwise
General Tolerance:
X ±0.40
X.x ±0.30
X.xx ±0.20
X° ±5°
X.x° ±3°Title: Wafer 5.70mm Pitch MX 180° DIP
With Lock Type Dual Dows Connector

Molde Code: GT-A5701WVD-2XXXXX01

DRAWN	CHECKED	APPROVED	DATE
Hu	Hu	Chen	2021.10.20

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 2/2

2	PIN MATERIAL	High Conductivity Copper Alloy	MATTE Tin
1	HOUSING	LCP,94V-0	BLACK
NO.	PART NAME	MATERIAL	REMARK



1

2

3

4

5