






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.03.04	



SPECIFICATIONS
1.OPERATING CURRENT:0.5A MAX.
2.OPERATION TEMPERATURE:-25 TO +85
3.DIELECTRIC WITHSTANDING VOLTAGE:
500Volts AC BETWEEN
ADIACENT TERMINAL(UNMATE)
300Volts AC BETWEEN
ADIACENT TERMINAL(MATE)
4.INSULATION RESISTANCE:
100Mohm MIN(UNMATED);10Mohm MIN.(MATED)
5.HDMI SPECIFICATION COMPLIANCE

A71-06H0-1X1N1

1:Au 1U"
5:Au 15U"
6:Au 30U"



RECOMMENDED PCB LAYOUT (TOP VIEW)
TOLERANCE: ±0.05mm
ORDER INFORMATION

4	DUST COVER	1	THERMOPLASTIC UL94V-0
3	CONTACTS	19	COPPER ALLOY, GOLD PLATED OVER NICKEL ON CONTACT AREA AND 100u" MIN. TIN PLATED OVER NICKEL ON SOLDER TAILS
2	HOUSING	1	THERMOPLASTIC UL94V-0
1	SHELL	1	COPPER ALLOY OR SPCC, NICKEL PLATED

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
HDMI CONNECTOR
PART NO.:
A71-06H0-1X1N1
DWG NO.: