

1

2

3

4

A

B

C




D

A

B

C

D



产品字码标识

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 葚


规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: ≤ 30 m Ω
- 绝缘电阻 Insulation resistance: ≥ 100 M Ω (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: 500 ± 150 gf
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 23 P G-12 N 1 W W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 03-3A;
- ④ Switch Circuit: 23-2P3T;
- ⑤ P: Welding plates;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: N-Square enclosure;
- ⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red



DESIGN	桑 葚	VIEW: 	MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0323PG-12N1WW		
APPROVED		SIZE: A4	DWG NO.: X-SS-0323PG-12N1WW		
PRECISION CO.,LIMITED			SCALE N/A	PAGE 1 / 1	REVISION A0

1

2

3

4