









NOTE:

1. TERMINAL: COPPER ALLOY.
2. HOUSING: LCP UL 94V-0. COLOR: BLACK
PLATING:
1. 1.27um MIN. NI UNDERPLATING.
2. 0.38um GOLD PLATING ON CONTACT AREA.
3. RECOMMENDED MOUNTING HARDWARE: M2X1.35 SELF-THREADING SCREW
MOUNTING SCREW LENGTH: PCB THICKNESS+3.0MM MAX(1.75MM MIN)
MOUNTING HARDWARE NOT SUPPLIED

TOLERANCE	
LINEAR	ANGLES
X.±0.30	X'±
.X±0.25	.X'±
.XX±0.15	.XX'±
.XXX±0.08	.XXX'±

UMax 东莞市友贸实业有限公司
conn DONGGUAN UMAXCONN ENTERPRISE LIMITED

TITLE: 24G MINI SAS HD INTEGRATED CONNECTOR,
0.75 PITCH, R/A, PRESS FIT TYPE

PART NO. 91905-100151T

DWG NO. 9190507301

UNITS	SCALE	SHEET	REV
MM	1 : 1	1 OF 1	A1

REV	ECN NO.	NAME	DATE
A1	---	Lei Songping	May,09.2017

APPD: Jason MAT'L:
CHKD: Schumi FINISH:
DRWN: Lucy Q'TY: