




■ Specifications :

- Voltage rating: 250 V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m \Omega$
- After environmental testing : $\leq 20m \Omega$

X3025 W R S-2x03 D -LP SW

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Straight 180°
- ④ Welding Way: S-SMT
- ⑤ Row No.-Pin No.: 2*XX-2*02P~2*22P
- ⑥ Plug the Pin & Special No.: D-With Solder Tabs
- ⑦ Material: LP-LCP 94V-0
- ⑧ Plating Category: SN-Bright Tin Plating;
G05-Contact Gold 5u"
SW-Fog Tin plating
- ⑨ Color : Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	6.65	---	2*07	24.65	18.00
2*02	9.65	3.00	2*08	27.65	21.00
2*03	12.65	6.00	2*09	30.65	24.00
2*04	15.65	9.00	2*10	33.65	27.00
2*05	18.65	12.00	2*11	36.65	30.00
2*06	21.65	15.00	2*12	39.65	33.00

X3025WRS-2x03D-LPSW	LCP UL 94V-0	Brass	Matte Tin	Brass	Tin-Plated	X3025H
X3025WRS-2x03D-LPG05			Ni-5.0u"Min; Sn-120u"Min; Contact Area Gold: 5u" Min.			
X3025WRS-2x03D-LPSN			Tin-Plated			
PART NO	Material	Material(Pin)	Finish(Pin)	Material(Solder Tabs)	Finish(Solder Tabs)	Mates With XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors			
				XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X30 25WRS-2x03D-LPSW			
Δx					 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X30 25WRS-2x03D-LPSW			
Δx					4<L  16	±0.3	APPD		DATE		SIZE: A4				
Δx					16<L  63	±0.4			DATE						
MARK	DESCRIPTION			DATE	REVISED	APPROVED									
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.helloxkb.com													1.0g	1/1	A0