







NOTES

1.MATERIAL

- 1.1HOUSING: THERMOPLASTIC.U194V-0. COLOR:BLACK
- 1.2CONTACT:HIGH-PERFORMANCE COPPER ALLOY.
- 1.3LATCH:STAINLESS STEEL.
- 1.4PEG: STAINLESS STEEL.

2.FINISH


- 2.1CONTACT:GOLD PLATING(SEE P/N) ON CONTACT AREA AND 1~3u" GOLD PLATING ON SOLDER AREA NICKEL 50~150u"UNDER-PLATING ALL OVER
- 2.2PEG:50~150u" TIN PLATING OVER 50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL:MSL(MOISTURE SENSITIVITY LEVEL)=1.

4.PRODUCT NUMBER NOTE:

D5262-52 XX S R

- 52: 5.2mm HEIGHT
- CONTACT AREA PLATING
- 01: G/F
- 10: 10u"Au
- 15: 15u"Au
- PACKING OPTIONS
- R: TAPE&REEL
- ORIENTATION
- S: STANDARD
- R: REVERSE




MATING: ① INSERTING → ② ROTATING → ③ FIXED



UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

MATING/UNMATING VIEW

SCALE 2:1

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		APPD: Jason		MAT'L:	
LINEAR	ANGLES						
X.±0.40	X°±	.XX±0.20		.XX°±		CHKD: Schumi	
.X±0.30	.X°±						
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±	DRWN:Lei Songping	


TITLE:		DDR5 SODIMM 5.2H 262PIN STANDARD TYPE.			
PART NO.		D5262-52XXSR			
DWG NO.		C-D5262-52S			
	UNITS	SCALE	SHEET	REV	
	MM	1 : 1	1 OF 2	A	



Technical drawing of a mechanical part with the following dimensions and features:

- Overall width: 4.00 ± 0.15
- Top flange width: 1.00 ± 0.05
- Section line: **-A-**
- Overall height: 4.00 ± 0.10
- Left side height: 4.20 Min.
- Internal step height: 4.00 Min.
- Feature: **FULL R** (fillet)
- Detail view (circled): $2 \times C0.25 \text{ Max.}$
- Surface texture symbol: 1.125

DETAIL D
SCALE 2:1



DETAIL G
SCALE 2:1


2.55+0.15
0.30Max.

0.50


262x0.35+0.03

0.10	C	B	A
0.05	C		

DETAIL E
SCALE 2:1



DETAIL F
SCALE 2:1



DETAIL H
SCALE 1:1

TITLE:	DDR5 SODIMM 5.2H 262PIN STANDARD TYPE.
--------	---

PART NO.	D5262-52XXSR
----------	--------------

DWG NO.	C-D5262-52S
---------	-------------

	UNITS	SCALE	SHEET	REV
	MM	1 : 1	2 OF 2	A