






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.12	阿树



First Circuit mark
(not showing
on 4 and 6
Circuits series)





Specifications:
规格:
Voltage rating:400V AC/DC
额定电压: 400V AC/DC
Current rating:14A AC/DC
额定电流: 14A AC/DC
Withstanding voltage:1800V AC/minute
耐受电压: 1800V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:15mΩ Max
接触电阻: 15mΩ Max

PART NO.:

X3501 W R-2x03 A-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No.Pin No:2xXX-2x02~2x08P
- ⑤Category:A Key Black ; B Key Nature
- ⑥Material:LP-LCP UL94V-0
- ⑦Plating:SN-Tin Plated or V01-Gold Flash

Poles	Dimensions		
	A	B	C
2x02	3.50	8.00	/
2x03	7.00	11.50	/
2x04	10.50	15.00	7.00
2x05	14.00	18.50	10.50
2x06	17.50	22.00	14.00
2x07	21.00	25.50	17.50
2x08	24.50	29.00	21.00



X3501WR-2x03A-LPSN	LCP	Copper Alloy	WR-2xXXA	X3501H-2xXXA / X3501H-2xXXA0
			WR-2xXXB	X3501H-2xXXB / X3501H-2xXXB0
PART NO	Material	Material(Pin)	Category	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 3.5mm Crimp Style Connector		
PART NO.: X3501WR-2x03A-LPSN		
DWG NO.: X-X3501WR-2x03A-LPSN		
SCALE	PAGE	REVISION
N/A	1/1	A1