





Current Rating:	1.5 Amp
Insulation Resistance:	1000M ohms min
Contact Resistance:	20M ohms max
Dielectric Withstanding:	AC500V
Operating Temperature:	-65°C to +125°C
Contact Material:	Brass
Insulator Material:	PA6T,UL 94V-0 Black

PHDM06 - $\frac{X}{(1)} - \frac{X}{(2)} - \frac{X}{(3)} - \frac{D}{(4)} - \frac{A - C - D - W}{(5)} - \frac{X}{(6)} - \frac{X}{(7)} - \frac{X}{(8)} - \frac{X}{(9)}$

- ① Series No:
- ② No. of Contacts
02 To 80
- ③ Contact Plating:
G0: Gold flash S0: Selective
G1: 3U" Gold S1: Selective 3u"
G2: 5u" Gold S2: Selective 5u"
G3: 10u" Gold S3: Selective 10u"
G4: 15u" Gold S4: Selective 15u"
G5: 30u" Gold S5: Selective 30u"
SN: Tin
- ④ Connector Type
D: Dual
- ⑤ Pin Length:
A: 0400=4.00mm
C: 0517=5.17mm
D: 0075=0.75mm
W: 0650=6.50mm
- Please mark the desired
length in the A/C/D/W
- ⑥ Insulator Material
A: PBT B: PA6T
C: LCP D: PA46
E: PA9T
- ⑦ Packing
A: Tray
B: Bag
T: Tube
U: Tube+CAP
R: Tape&Reel
W: Tape&Reel+CAP
- ⑧ With locating pegs option
A: Type A without pegs
B: Type B with pegs
- ⑨ Plastic High
H1: 1.5mm
H2: 2.0mm

Standard IE P/N :

PHDM06-10-G0-D-0400-0517-0075-0650-B-B-A-H1

				A	C	D	W	Unless Otherwise specified tolerance	
				X. ± 0.35 X.XX: ± 0.20 X.X: ± 0.25 X.XXX: ± 0.15					
Pin (Per Row)	2-15P	16-25P	26-40P	4.00	5.17	0.75	6.50		
M	0.10	0.15	0.18	Optional			SCALE: As Shown		UNIT: mm

Antenk® ANTENK ELECTRONICS CO.,LTD
Http://www.antenk.com
E-mail:sales@antenk.com

						OPTIONAL	AS SHOWN	DATE	TITLE: 2.00mm Pin Header DualRow Double Plastic SMT Type
A2	Increase the flatness					2026/01/30	YUJUNJI	2026/01/30	
	Increase packing method and material					2016/10/25	CHECK BobYang	DATE 2026/01/30	
REV	DESCRIPTION					DATE	 3rd ANGLE PROJECTION		DRAWING NO: PHDM06-XXD-0400-0517-0075-0650-XXXX
									PRODUCT NO: PHDM06-XXD-0400-0517-0075-0650-XXXX

