








REV.	DESCRIPTION	ECN NO.	NAME	DATE



P.C.B LAYOUT



SPECIFICATION:
1.MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm
PEG: BRASS C2680R-H,T=0.30mm
2.FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG:100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN® 		
DIM.	TOL.	TITLE: SATA 7+15P 欧盟款 单排脚 直立式180°						
.X	±0.30	DWG. NO.: SATA-22M-17HM01						
.XX	±0.20							
.XXX	±0.05							
GENERAL ANGLE:		PART NO.: SATA-22M-17HM01						
.X°	±3°	DRAWN: ELLA						
.XX°	±2°							
.XXX°	±0.5°							
		UNIT:	SCALE:	SHEET:	DWG. SIZE:		LAYER:	APPROVED: WILL
		mm	none	1 of 1	A4		bxconn	