





| REVISIONS |         |          |             |            |
|-----------|---------|----------|-------------|------------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION | DATE       |
| A1        | N/A     |          | 图面升级整理图面    | 2025.02.26 |
| A2        | N/A     |          | 产品电气性能变更    | 2025.12.23 |



规格 Specifications:  
额定电压 Voltage rating:500VAC/DC.  
额定电流 Current rating:2A AC/DC  
耐电压 Withstanding voltage:500V AC/minute  
温度区间 Temperature range:-40℃to+125℃  
绝缘电阻 Insulation resistance:≥1000MΩ Min  
接触电阻 Contact resistance:≤20MΩ Max  
材料 Material: PA6T UL94V-0  
镀层 Plating Category: 1U"Gold  
波峰焊温度 Wave soldering temperature:255±5℃,10s

PART NO.:

X4622 W R-2x11 K L-C13 D50  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No.Pin No:2xXX-2x01~2x40P
- ⑤Plastic height: K=1.5mm
- ⑥L-Type L
- ⑦Plastic length: C=1.3mm
- ⑧Plastic length: D=5.0mm

|                       |              |               |                                     |                     |
|-----------------------|--------------|---------------|-------------------------------------|---------------------|
| X4622WR-2x11KL-C13D50 | PA6T UL94V-0 | Brass         | 1U"Gold                             | X4622F              |
| PART NO               | Material     | Material(Pin) | Finish(Pin)                         | Suitable XKB Female |
| DESIGN                | 阿树           | VIEW:         | MODEL TYPE:<br>2.0mm BTB Connector  |                     |
| CHECKED               |              | UNIT: mm/in   | PART NO.:<br>X4622WR-2x11KL-C13D50  |                     |
| APPROVED              |              | SIZE: A4      | DWG NO.:<br>X-X4622WR-2x11KL-C13D50 |                     |
| SCALE                 |              |               | PAGE                                | REVISION            |
| N/A                   |              |               | 1/1                                 | A2                  |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERAUCES |       |



XKB INDUSTRIAL PRECISION CO.,LIMITED