
Silicon Carbide (SiC) Cascode JFET – EliteSiC, Power N-Channel, D2PAK-3, 650 V, 27 mohm

UF3C065030B3



D²PAK-3 (TO-263, 3-LEAD)
CASE 418AJ

Description

This SiC FET device is based on a unique 'cascode' circuit configuration, in which a normally-on SiC JFET is co-packaged with a Si MOSFET to produce a normally-off SiC FET device. The device's standard gate-drive characteristics allows for a true "drop-in replacement" to Si IGBTs, Si FETs, SiC MOSFETs or Si superjunction devices. Available in the D²PAK-3 package, this device exhibits ultra-low gate charge and exceptional reverse recovery characteristics, making it ideal for switching inductive loads when used with recommended RC-snubbers, and any application requiring standard gate drive.


Features

- Typical On-resistance $R_{DS(on),typ}$ of 27 mΩ
- Maximum Operating Temperature of 175°C
- Excellent Reverse Recovery
- Low Gate Charge
- Low Intrinsic Capacitance
- High Pulse Current Capability
- ESD Protected, HBM Class 2
- Very Low Switching Losses (Required RC-snubber Loss Negligible under Typical Operating Conditions)
- This Device is Halogen Free and RoHS Compliant with Exemption 7a, Pb−Free 2LI (on second level interconnection)

Typical Applications


- EV Charging
- PV Inverters
- Switch Mode Power Supplies
- Power Factor Correction Modules
- Motor Drives
- Induction Heating

MARKING DIAGRAM



UF3C065030B3	= Specific Device Number
A	= Assembly Location
YY	= Year
WW	= Work Week
ZZZ	= Lot ID

PIN CONNECTIONS



ORDERING INFORMATION

See detailed ordering and shipping information on page 9 of this data sheet.

© Semiconductor Components Industries, LLC, 2024

MAXIMUM RATINGS

Parameter	Symbol	Test Conditions	Value	Unit
Drain-source Voltage	V_{DS}		650	V
Gate-source Voltage	V_{GS}	DC	−25 to +25	V
Continuous Drain Current (Note 1)	I_D	T_C = 25 °C	65	A
		T_C = 100 °C	47	
Pulsed Drain Current (Note 2)	I_{DM}	T_C = 25 °C	230	A
Single Pulsed Avalanche Energy (Note 3)	E_{AS}	L = 15 mH, I_{AS} = 4 A	120	mJ
Power Dissipation	P_{tot}	T_C = 25 °C	242	W
Maximum Junction Temperature	$T_{J,max}$		175	°C
Operating and Storage Temperature	T_J, T_{STG}		−55 to 175	°C
Reflow Soldering Temperature	T_{solder}	Reflow MSL 1	245	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Limited by $T_{J,max}$
2. Pulse width t_p limited by $T_{J,max}$
3. Starting T_J = 25 °C

THERMAL CHARACTERISTICS

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$		–	0.48	0.62	°C/W

ELECTRICAL CHARACTERISTICS (T_J = +25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
TYPICAL PERFORMANCE – STATIC							
Drain-source Breakdown Voltage	BV_{DS}	V_{GS} = 0 V, I_D = 1 mA		650	–	–	V
Total Drain Leakage Current	I_{DSS}	V_{DS} = 650 V, V_{GS} = 0 V, T_J = 25 °C		–	6	150	μA
		V_{DS} = 650 V, V_{GS} = 0 V, T_J = 175°C		–	30	–	
Total Gate Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = −20 V / +20 V		–	6	±20	μA
Drain-source On-resistance	$R_{DS(on)}$	V_{GS} = 12 V, I_D = 40 A	T_J = 25 °C	–	27	35	mΩ
			T_J = 125 °C	–	35	–	
			T_J = 175 °C	–	43	–	
Gate Threshold Voltage	$V_{G(th)}$	V_{DS} = 5 V, I_D = 10 mA		4	5	6	V
Gate Resistance	R_G	f = 1 MHz, open drain		–	4.5	–	Ω
TYPICAL PERFORMANCE – REVERSE DIODE							
Diode Continuous Forward Current (Note 1)	I_S	T_C = 25 °C		–	–	65	A
Diode Pulse Current (Note 2)	$I_{S,pulse}$	T_C = 25 °C		–	–	230	A
Forward Voltage	V_{FSD}	V_{GS} = 0 V, I_S = 20 A, T_J = 25 °C		–	1.3	1.4	V
		V_{GS} = 0 V, I_S = 20 A, T_J = 175 °C		–	1.35	–	
Reverse Recovery Charge	Q_{rr}	V_R = 400 V, I_S = 40 A, V_{GS} = −5 V, R_{G_EXT} = 22 Ω, di/dt = 1500 A/μs, T_J = 25 °C		–	211	–	nC
Reverse Recovery Time	t_{rr}			–	34	–	ns
Reverse Recovery Charge	Q_{rr}	V_R = 400 V, I_S = 40 A, V_{GS} = −5 V, R_{G_EXT} = 22 Ω, di/dt = 1500 A/μs, T_J = 150 °C		–	188	–	nC
Reverse Recovery Time	t_{rr}			–	32	–	ns

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (T_J = +25 °C unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
TYPICAL PERFORMANCE – DYNAMIC						
Input Capacitance	C_{iss}	V_{DS} = 100 V, V_{GS} = 0 V, f = 100 kHz	–	1500	–	pF
Output Capacitance	C_{oss}		–	293	–	
Reverse Transfer Capacitance	C_{rss}		–	2	–	
Effective Output Capacitance, Energy Related	$C_{oss(er)}$	V_{DS} = 0 V to 400 V, V_{GS} = 0 V	–	215	–	pF
Effective Output Capacitance, Time Related	$C_{oss(tr)}$		–	480	–	
C_{OSS} Stored Energy	E_{oss}	V_{DS} = 400 V, V_{GS} = 0 V	–	17.5	–	μJ
Total Gate Charge	Q_G	V_{DS} = 400 V, I_D = 40 A, V_{GS} = −5 V to 15 V	–	51	–	nC
Gate-drain Charge	Q_{GD}		–	11	–	
Gate-source Charge	Q_{GS}		–	19	–	
Turn-on Delay Time	$t_{d(on)}$	V_{DS} = 400 V, I_D = 40 A, Gate Driver = −5 V to +15 V, Turn-on $R_{G,EXT}$ = 1.8 Ω, Turn-off $R_{G,EXT}$ = 22 Ω, Inductive Load, FWD: same device with V_{GS} = −5 V and R_G = 22 Ω, RC snubber: R_S = 5 Ω and C_S = 330 pF, T_J = 25 °C	–	34	–	ns
Rise Time	t_r		–	16	–	
Turn-off Delay Time	$t_{d(off)}$		–	56	–	
Fall Time	t_f		–	15	–	
Turn-on Energy including R_S Energy (Note 4)	E_{ON}		–	392	–	μJ
Turn-off Energy including R_S Energy (Note 4)	E_{OFF}		–	113	–	
Total Switching Energy including R_S Energy (Note 4)	E_{TOTAL}		–	505	–	
Snubber R_S Energy during Turn-on	E_{RS_ON}		–	5.3	–	
Snubber R_S Energy during Turn-off	E_{RS_OFF}		–	7.9	–	
Turn-on Delay Time	$t_{d(on)}$	V_{DS} = 400 V, I_D = 40 A, Gate Driver = −5 V to +15 V, Turn-on $R_{G,EXT}$ = 1.8 Ω, Turn-off $R_{G,EXT}$ = 22 Ω, Inductive Load, FWD: same device with V_{GS} = −5 V and R_G = 22 Ω, RC snubber: R_S = 5 Ω and C_S = 330 pF, T_J = 150 °C	–	32	–	ns
Rise Time	t_r		–	16	–	
Turn-off Delay Time	$t_{d(off)}$		–	57	–	
Fall Time	t_f		–	16	–	
Turn-on Energy including R_S Energy (Note 4)	E_{ON}		–	370	–	μJ
Turn-off Energy including R_S Energy (Note 4)	E_{OFF}		–	118	–	
Total Switching Energy including R_S Energy (Note 4)	E_{TOTAL}		–	488	–	
Snubber R_S Energy during Turn-on	E_{RS_ON}		–	4.6	–	
Snubber R_S Energy during Turn-off	E_{RS_OFF}		–	8.2	–	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The switching performance are evaluated with a RC snubber circuit as shown in Figure 29.

Share Feedback
Your Opinion Matters

TYPICAL PERFORMANCE DIAGRAMS




Figure 1. Typical Output Characteristics at T_J = −55 °C, t_p < 250 μs




Figure 2. Typical Output Characteristics at T_J = 25 °C, t_p < 250 μs




Figure 3. Typical Output Characteristics at T_J = 175 °C, t_p < 250 μs




Figure 4. Normalized On-Resistance vs. Temperature at V_{GS} = 12 V and I_D = 40 A




Figure 5. Typical Drain-Source On-Resistances at V_{GS} = 12 V




Figure 6. Typical Transfer Characteristics at V_{DS} = 5 V

Share Feedback
Your Opinion Matters

TYPICAL PERFORMANCE DIAGRAMS (CONTINUED)




Figure 7. Threshold Voltage vs. Junction Temperature at V_{DS} = 5 V and I_D = 10 mA




Figure 8. Typical Gate Charge at V_{DS} = 400 V and I_D = 40 A




Figure 9. 3rd Quadrant Characteristics at T_J = −55 °C




Figure 10. 3rd Quadrant Characteristics at T_J = 25 °C




Figure 11. 3rd Quadrant Characteristics at T_J = 175 °C




Figure 12. Typical Stored Energy in C_{OSS} at V_{GS} = 0 V

Share Feedback
Your Opinion Matters

TYPICAL PERFORMANCE DIAGRAMS (CONTINUED)




Figure 13. Typical Capacitances at f = 100 kHz and V_{GS} = 0 V




Figure 14. DC Drain Current Derating




Figure 15. Total Power Dissipation




Figure 16. Maximum Transient Thermal Impedance




Figure 17. Safe Operation Area at T_C = 25 °C, D = 0, Parameter t_p




Figure 18. Reverse Recovery Charge Q_{rr} vs. Junction Temperature

Share Feedback
Your Opinion Matters

TYPICAL PERFORMANCE DIAGRAMS (CONTINUED)




Figure 19. Clamped Inductive Switching Energy vs. Drain Current at T_J = 25 °C, Turn-on R_{G_EXT} = 1.8 Ω and Turn-off R_{G_EXT} = 22 Ω




Figure 20. RC Snubber Energy Loss vs. Drain Current at the Test Conditions shown in Figure 19




Figure 21. Clamped Inductive Switching Turn-On Energy including RC Snubber Energy Loss as a Function of Total External Turn-on Gate Resistor R_{G_EXT}




Figure 22. RC Snubber Energy Loss as a Function of Total External Turn-on Gate Resistor R_{G_EXT} at the Test Conditions shown in Figure 21




Figure 23. Clamped Inductive Switching Turn-Off Energy including RC Snubber Energy Loss as a Function of Total External Turn-off Gate Resistor R_{G_EXT}




Figure 24. RC Snubber Energy Loss as a Function of Total External Turn-off Gate Resistor R_{G_EXT} at the Test Conditions shown in Figure 23

Share Feedback
Your Opinion Matters

TYPICAL PERFORMANCE DIAGRAMS (CONTINUED)




Figure 25. Clamped Inductive Switching Energy including RC Snubber Energy Loss as a Function of Junction Temperature at I_D = 40 A




Figure 26. RC Snubber Energy Loss as a Function of Junction Temperature at the Test Conditions shown in Figure 25




Figure 27. Clamped Inductive Switching Energy including RC Snubber Energy Loss as a Function of Snubber Capacitance at I_D = 40 A and T_J = 25 °C




Figure 28. RC Snubber Energy Loss as a Function of Snubber Capacitance at the Test Conditions shown in Figure 27




Figure 29. Clamped Inductive Load Switching Test Circuit. An RC Snubber (R_S = 5 Ω and C_S = 330 pF) is required to Improve the Turn-off Waveforms.

Share Feedback
Your Opinion Matters

APPLICATIONS INFORMATION

SiC FETs are enhancement-mode power switches formed by a high-voltage SiC depletion−mode JFET and a low-voltage silicon MOSFET connected in series. The silicon MOSFET serves as the control unit while the SiC JFET provides high voltage blocking in the off state. This combination of devices in a single package provides compatibility with standard gate drivers and offers superior performance in terms of low on-resistance ($R_{DS(on)}$), output capacitance (C_{oss}), gate charge (Q_G), and reverse recovery charge (Q_{rr}) leading to low conduction and switching losses. The SiC FETs also provide excellent reverse conduction capability eliminating the need for an external anti-parallel diode.

Like other high performance power switches, proper PCB layout design to minimize circuit parasitics is strongly recommended due to the high dv/dt and di/dt rates. An external gate resistor is recommended when the FET is working in the diode mode in order to achieve the optimum reverse recovery performance. For more information on SiC FET operation, see www.onsemi.com.

A snubber circuit with a small $R_{(G)}$, or gate resistor, provides better EMI suppression with higher efficiency compared to using a high $R_{(G)}$ value. There is no extra gate delay time when using the snubber circuitry, and a small $R_{(G)}$ will better control both the turn-off $V_{(DS)}$ peak spike and ringing duration, while a high $R_{(G)}$ will damp the peak spike but result in a longer delay time. In addition, the total switching loss when using a snubber circuit is less than using high $R_{(G)}$, while greatly reducing $E_{(OFF)}$ from mid-to-full load range with only a small increase in $E_{(ON)}$. Efficiency will therefore improve with higher load current. For more information on how a snubber circuit will improve overall system performance, visit the **onsemi** website at www.onsemi.com.

ORDERING INFORMATION


Part Number	Marking	Package	Shipping†
UF3C065030B3	UF3C065030B3	D^2PAK−3 (TO−263, 3−LEAD)	800 units / Tape and Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


Share Feedback
Your Opinion Matters

D²PAK–3 (TO–263, 3–LEAD)
CASE 418AJ
ISSUE F

DATE 11 MAR 2021



SCALE 1:1




RECOMMENDED
MOUNTING FOOTPRINT


* For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: INCHES
3. CHAMFER OPTIONAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.005 PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY AT DATUM H.
5. THERMAL PAD CONTOUR IS OPTIONAL WITHIN DIMENSIONS E, L1, D1, AND E1.
6. OPTIONAL MOLD FEATURE.
7. ①, ② … OPTIONAL CONSTRUCTION FEATURE CALL OUTS.


	INCHES		MILLIMETERS	
DIM	MIN.	MAX.	MIN.	MAX.
A	0.160	0.190	4.06	4.83
A1	0.000	0.010	0.00	0.25
b	0.020	0.039	0.51	0.99
c	0.012	0.029	0.30	0.74
c2	0.045	0.065	1.14	1.65
D	0.330	0.380	8.38	9.65
D1	0.260	---	6.60	---
E	0.380	0.420	9.65	10.67
E1	0.245	---	6.22	---
e	0.100 BSC		2.54 BSC	
H	0.575	0.625	14.60	15.88
L	0.070	0.110	1.78	2.79
L1	---	0.066	---	1.68
L2	---	0.070	---	1.78
L3	0.010 BSC		0.25 BSC	
M	0°	8°	0°	8°








DETAIL C
TIP LEADFORM
ROTATED 90° CW



VIEW A–A

VIEW A–A
OPTIONAL CONSTRUCTIONS

GENERIC MARKING DIAGRAMS*



IC **Standard** **Rectifier** **SSG**

XXXXXX = Specific Device Code
A = Assembly Location
WL = Wafer Lot
Y = Year
WW = Work Week
W = Week Code (SSG)
M = Month Code (SSG)
G = Pb–Free Package
AKA = Polarity Indicator

*This information is generic. Please refer to device data sheet for actual part marking. Pb–Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON56370E**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**D²PAK–3 (TO–263, 3–LEAD)**	**PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2011

onsemi, , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales