

P-Ch 60V Fast Switching MOSFETs

- ★ 100% EAS Guaranteed
- ★ Green Device Available
- ★ Super Low Gate Charge
- ★ Excellent CdV/dt effect decline
- ★ Advanced high cell density Trench technology

Product Summary




BVDSS	RDSON	ID
-60V	3.3Ω	-0.17A

Description

The BSS84 is the high cell density trenched P-ch MOSFETs, which provides excellent RDSON and gate charge for most of the synchronous buck converter applications.

The BSS84 meets the RoHS and Green Product requirements with full function reliability approved.

SOT23 Pin Configurations



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-60	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D @ T_A = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ -4.5\text{V}^1$	-0.17	A
$I_D @ T_A = 70^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ -4.5\text{V}^1$	-0.14	A
I_{DM}	Pulsed Drain Current ²	-1.2	A
$P_D @ T_A = 25^\circ\text{C}$	Total Power Dissipation ³	0.35	W
$P_D @ T_A = 70^\circ\text{C}$	Total Power Dissipation ³	---	W
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	357	°C/W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹ ($t \leq 10\text{s}$)	---	---	°C/W

Electrical Characteristics ($T_J=25\text{ }^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=-250\mu A$	-60	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to 25°C , $I_D=-1\text{mA}$	---	---	---	V/ $^{\circ}\text{C}$
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=-10V$, $I_D=-0.15A$	---	3.3	8	Ω
		$V_{GS}=-4.5V$, $I_D=-0.15A$	---	3.5	9.9	
		$V_{GS}=-2.5V$, $I_D=-0.15A$	---	---	---	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=-250\mu A$	-0.9	-1.4	-2.0	V
$\Delta V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	---	---	mV/ $^{\circ}\text{C}$
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-60V$, $V_{GS}=0V$, $T_J=25^{\circ}\text{C}$	---	---	-1	μA
		$V_{DS}=-60V$, $V_{GS}=0V$, $T_J=55^{\circ}\text{C}$	---	---	---	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=-5V$, $I_D=-3A$	---	---	---	S
Q_g	Total Gate Charge (-4.5V)	$V_{DS}=-30V$, $V_{GS}=-10V$, $I_D=-0.15A$	---	1.77	---	nC
Q_{gs}	Gate-Source Charge		---	0.57	---	
Q_{gd}	Gate-Drain Charge		---	0.18	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=-30V$, $V_{GS}=-4.5V$, $R_G=2.5\Omega$, $I_D=-0.15A$	---	8.6	---	ns
T_r	Rise Time		---	20	---	
$T_{d(off)}$	Turn-Off Delay Time		---	15	---	
T_f	Fall Time		---	77	---	
C_{iss}	Input Capacitance	$V_{DS}=-30V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	43	---	pF
C_{oss}	Output Capacitance		---	2.9	---	
C_{rss}	Reverse Transfer Capacitance		---	1.8	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,4}	$V_G=V_D=0V$, Force Current	---	---	-0.17	A
I_{SM}	Pulsed Source Current ^{2,4}		---	---	---	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=-0.17A$, $T_J=25^{\circ}\text{C}$	---	---	-1.2	V
t_{rr}	Reverse Recovery Time	$I_F=-0.15A$, $di/dt=100A/\mu s$	---	23	---	nS
Q_{rr}	Reverse Recovery Charge	μs , $T_J=25^{\circ}\text{C}$	---	13	---	nC

Note :

- A. Pulse Test: Pulse Width $\leq 10\mu s$, Duty cycle $\leq 2\%$.
 B. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch.

■ Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Drain-Source on Resistance




Figure4. Drain-Source on Resistance




Figure5. Diode Forward Voltage vs. current




Figure6. Gate Threshold vs. Junction Temperature




Figure7. Capacitance Characteristics





Figure8. Normalized On-Resistance

SOT23 Mechanical Data



DIMENSIONS (unit : mm)

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	0.90	1.01	1.15	A₁	0.01	0.05	0.10
b_p	0.30	0.42	0.50	c	0.08	0.13	0.15
D	2.80	2.92	3.00	E	1.20	1.33	1.40
e	--	1.90	--	e₁	--	0.95	--
H_E	2.25	2.40	2.55	L_p	0.30	0.42	0.50
Q	0.45	0.49	0.55	v	--	0.20	--
w	--	0.10	--				