



“*” Pivot Dimension

所用物料均符合ROHS标准




MATERIALS AND FINISH

SHELL : STEEL MATERIAL, FRONT NICKEL FINISHED
BACK SHELL TIN FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR
CONTACT MATERIAL : PHOSCU
CONTACT FINISH : FULL GOLD 1u" FINISHED
#4-40 THREADED RIVETS

ELECTRICAL CHARACTERISTICS

CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C ~ +105°C



TEL: 0769-85321601					
FAX: 0769-85321609					
未注公差		GDM78F-180-4		DRAWING :	DATE :
X. ±0.2				Roy	2009. 10. 08
X.X ±0.1				CHECKED :	DATE :
X.XX ±0.05					2009. 10. 08
X.XXX ±0.03		Drawing No.		APPROVED :	DATE :
X.* ±2° X.X* ±1°		Part No.			2009. 10. 08
—		Fixture No.			
A/O版					