






High photosynthesis 台高(H)	The female seat height(H1)	The male seat height(H2)	Insertion height(H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



Part No	CKT	A	B	C	D	E
XY-DF840A-8LBGDW	8	2.40	3.45	5.10	4.20	4.00
XY-DF840A-10LBGDW	10	3.20	4.25	5.90	5.00	
XY-DF840A-12LBGDW	12	4.00	5.05	6.70	5.80	
XY-DF840A-14LBGDW	14	4.80	5.85	7.50	6.60	
XY-DF840A-16LBGDW	16	5.60	6.65	8.30	7.40	
XY-DF840A-18LBGDW	18	6.40	7.45	9.10	8.20	
XY-DF840A-20LBGDW	20	7.20	8.25	9.90	9.00	
XY-DF840A-22LBGDW	22	8.00	9.05	10.70	9.80	
XY-DF840A-24LBGDW	24	8.80	9.85	11.50	10.60	8.00
XY-DF840A-26LBGDW	26	9.60	10.65	12.30	11.40	
XY-DF840A-28LBGDW	28	10.40	11.45	13.10	12.20	
XY-DF840A-30LBGDW	30	11.20	12.25	13.90	13.00	
XY-DF840A-32LBGDW	32	12.00	13.05	14.70	13.80	
XY-DF840A-34LBGDW	34	12.80	13.85	15.50	14.60	
XY-DF840A-36LBGDW	36	13.6	14.65	16.30	15.40	
XY-DF840A-38LBGDW	38	14.40	15.45	17.10	16.20	
XY-DF840A-40LBGDW	40	15.20	16.25	17.90	17.00	
XY-DF840A-44LBGDW	44	16.80	17.85	19.50	18.60	
XY-DF840A-50LBGDW	50	19.20	20.25	21.90	21.00	
XY-DF840A-60LBGDW	60	23.20	24.25	25.90	25.00	
XY-DF840A-70LBGDW	70	27.20	28.25	29.90	29.00	
XY-DF840A-80LBGDW	80	31.20	32.25	33.90	33.00	
XY-DF840A-100LBGDW	100	39.20	40.25	41.90	41.00	

序号	品名	材质
①	0.8 Pitch 双排立式 BTB 公座板芯	PA10T UL94 V-0, 颜色: 黑色
②	0.8 Pitch 双排立式 BTB 公座端子	铜合金/表面镀金
③	0.8 Pitch 双排立式 BTB 公座插座	LCP UL94 V-0, 颜色: 黑色

DIMENSION IN mm	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X±0.5	X.*±1°
.XX±0.2	.X.*±
.XXX±0.1	.XX.*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co., Ltd

APR. Alex	TITLE: 0.8 Pitch 双排立式 BTB 公座板芯 (单排 4.0)
CHK. Jack	DWG NO. XY-DF840A-NLBGDW
DRA. Can	PROJ. CUSTOMER DRAWING
SIZE A4	SCALE 1:1
SHEET 1/1	REV. A