






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.27	阿树



- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:800V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

- PART NO.:
- X2026 W R-2x11 A-N0 SN
① ② ③ ④ ⑤ ⑥ ⑦
- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:2xXX-2x02~2x20Pin
⑤Plug the Pin&Special NO:
A-With Lock on both side
⑥Material:9T-PA9T 94V-0;
N0-PA66 94V-0
⑦Plating Category:SN-Bright Tin Plating



poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	8.00	4.60	2x09	16.00	22.00	18.60	2x16	30.00	36.00	32.60
2x03	4.00	10.00	6.60	2x10	18.00	24.00	20.60	2x17	32.00	38.00	34.60
2x04	6.00	12.00	8.60	2x11	20.00	26.00	22.60	2x18	34.00	40.00	36.60
2x05	8.00	14.00	10.60	2x12	22.00	28.00	24.60	2x19	36.00	42.00	38.60
2x06	10.00	16.00	12.60	2x13	24.00	30.00	26.60	2x20	38.00	44.00	40.60
2x07	12.00	18.00	14.60	2x14	26.00	32.00	28.60				
2x08	14.00	20.00	16.60	2x15	28.00	34.00	30.60				

X2026WR-2xXXA-9TSN	PA9T UL 94V-0	Brass	Tin-Plated	X2026H-A
X2026WR-2x11A-N0SN	PA66 UL 94V-0			X2026H-A
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.: X2026WR-2x11A-N0SN
APPROVED		SIZE:	A4	DWG NO.: