

Glass Passivated Three Phase Bridge Rectifiers

Voltage - 800 to 1600 V


Forward Current – 25A

FEATURES

- ♦Glass passivated die construction
- ♦Ideal for printed circuit boards
- ♦High surge current capability
- ♦High temperature soldering guaranteed:
265°C /10 seconds, 0.375" (9.5mm) lead
length, 5lbs. (2.3kg) tension

MECHANICAL DATA

- ♦Case: Molded plastic case
- ♦Terminals: Plated leads solderable per
MIL-STD-750, Method 2026
- ♦Polarity: Marked on Body
- ♦Mounting Position: Any



Maximum Ratings and Thermal Characteristics (TA = 25°C unless otherwise noted)

Conditions	Symbol	SGBJ2508	SGBJ2510	SGBJ2512	SGBJ2514	SGBJ2516	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	800	1000	1200	1400	1600	V
Maximum RMS voltage	V_{RMS}	900	1100	1300	1500	1700	V
Maximum DC Blocking Voltage	V_{DC}	800	1000	1200	1400	1600	V
average forward output current sine wave ,R-load Tc =100°C	I_D	25					A
Peak forward surge current single half sine-wave superimposed on rated load (JEDEC Method) 50Hz Tj=25°C	I_{FSM}	350					A
Rating for fusing (t=1~10ms)	I^2t	612					A ² s
A.C.50/60Hz;R.M.S.;1min	V_{ISO}	2500					V
Operating Junction and storage temperature range	T_j T_{stg}	-40 to +150					°C
Mounting Torque (Recommended torque:0.65 N • m)	M_s	0.8					N•m
Approximate Weight	W_t	10					g

Electrical Characteristics (TA = 25°C unless otherwise noted)

Conditions	Symbol	Values	Units
Maximum Forward Voltage per leg IF =12.5A Tj=25°C	V_{FM}	1.18	V
Maximum reverse current at rated blocking voltage per leg Tj = 150°C	I_{RRM}	3	mA
Maximum thermal resistance per ⁽¹⁾ per diode total	$R_{th(j-c)}$	9 1.5	°C/W

Notes: (1) Junction to case

Performance Curves







Fig.3 Max Non-Repetitive Surge Current

Marking Diagram



Ordering information

Package	Packing Description	Packing Quantity
SGBJ	bulk	200PCS/Box 2000PCS/Carton

Package Dimensions

SGBJ

Dim.	Millimeter(mm)		Dimensions in Inch	
	Min.	Max.	Min.	Max.
A	34.50	35.50	1.36	1.40
B	24.50	25.50	0.96	1.00
C	2.90	3.50	0.11	0.14
D	16.60	17.60	0.65	0.69
E	3.70	4.30	0.15	0.17
F	2.20	2.80	0.09	0.11
G	2.00	2.60	0.08	0.10
H	0.90	1.10	0.04	0.04
I	7.20	7.80	0.28	0.31
J	4.30	4.90	0.17	0.19
K	3.40	4.00	0.13	0.16
L	0.20	0.80	0.01	0.03
M	13.80	14.40	0.54	0.57
N	2.50	2.90	0.10	0.11
O	0.55	0.75	0.02	0.03

Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.