
REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.8	阿树



■SPECIFICATIONS
- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:1500V AC/minute
- Temperature range:−40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ
- After environmental testing:≤40mΩ

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	5.08	10.12	8.12	2x12	27.94	32.98	30.98
2x04	7.62	12.66	10.66	2x13	30.48	35.52	33.52
2x05	10.16	15.20	13.20	2x14	33.02	38.06	36.06
2x06	12.70	17.74	15.74	2x15	35.56	40.60	38.60
2x07	15.24	20.28	18.28	2x16	38.10	43.14	41.14
2x08	17.78	22.82	20.82	2x17	40.64	45.68	43.68
2x09	20.32	25.36	23.36	2x18	43.18	48.22	46.22
2x10	22.86	27.90	25.90	2x19	45.72	50.76	48.76
2x11	25.40	30.44	28.44	2x20	48.26	53.30	51.30

PART NO.:

X9555 W V S−2x05 E−9T V01 XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①Series No
②Category:W−Wafer
③Welding Board Angle:V−Stright 180°
④Welding Way:S−SMT
⑤Row No.Pin No:2xXX−2x03~2x20Pin
⑥Plug the Pin&Special NO: E−Matching 9555H−2xXXE HSG
⑦Material:PT−PBT 94V−0
9T−PA9T 94V−0
⑧Plating Category: VXX−All Gold−Plated
X01−Gold Flash
X05−Gold:5u" SN−Bright Tin Plating(70u")
⑨Color:Blank−Natural Color

PART NO	Material	Finish(Pin)	Finish(Pin)	Suitable XKB Terminal
X9555WVS−2x05E−9TV05	PA9T UL 94V−0	Brass	Gold:5U"	X9555H
X9555WVS−2x05E−PTSN			Tin−Plated	

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection

DESIGN	阿树	VIEW:	MODEL TYPE: 2.54mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9555WVS−2x05E−9TV01
APPROVED		SIZE: A4	DWG NO.: X−X9555WVS−2x05E−9TV01

SCALE	PAGE	REVISION
N/A	1/1	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED