

| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | 2024.05.09 | 桑 葚    |
|           |         |          |                 |            |        |


规格 Specification:

- 1.额定值 Rating:3A 125/250VAC  
2.接触电阻 Contact resistance:≤30 mΩ  
3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)  
4.电气寿命 Electronics life:>10000 cycles  
5.操作力 Operation force:500±150gf  
6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


SS-X 03 23 P G-6 N 5 W W  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;  
② Enclosure Material:  
A-Metal case;  
BLANK-Plastic case;  
③ Current Rating: 03-3A;  
④ Switch Circuit:23-2P3T;  
⑤ P: Welding plates;  
⑥ Handle Shape: G-Camber handle;  
⑦ Handle Height: 3~15mm;  
⑧ Enclosure Shape:N-Square enclosure;  
⑨ Terminal specs:  
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;  
4:TYPE-4; 5:TYPE-5;  
⑩ Handle Colour:  
B-Black; W-White; R-Red  
⑪ Housing Colour:  
B-Black; W-White; R-Red



产品字码标识

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |     |       |       |             |                   |
|----------|-----|-------|-------|-------------|-------------------|
| DESIGN   | 桑 葚 | VIEW: |       | MODEL TYPE: | SLIDE SWITCH      |
| CHECKED  |     | UNIT: | mm/in | PART NO.:   | SS-0323PG-6N5WW   |
| APPROVED |     | SIZE: | A4    | DWG NO.:    | X-SS-0323PG-6N5WW |
|          |     | SCALE | PAGE  | REVISION    |                   |
|          |     | N/A   | 1/1   | A0          |                   |

XKB INDUSTRIAL PRECISION CO.,LIMITED

