


SPECIFICATION

Physical Dimensions(尺寸图):

Unit(单位):mm



| Item(项目) | Dimension(尺寸) | Tolerance(公差范围) | Unit(单位) |
|----------|---------------|-----------------|----------|
| A        | 36.0          | ±1.0            | mm       |
| B        | 5.0           | ±0.5            | mm       |
| C        | 16.0          | ±0.7            | mm       |
| D        | 26.0          | ±0.7            | mm       |
| E        | 6.5           | ±0.5            | mm       |

Electrical requirements(电气特性):

Z1=10 Ω Min at 25 MHz ;Z2=40 Ω Min at 100 MHz

Electrical requirements(电气特性):

Testing Equipment(测试仪器) :E4991A + 16194A

Test frequency range(测试频率区间) :1-500MHz

Test lead set(测试线组) :Ø0.5x0.5TSx100L(mm)

| Model.(型号)   | Unit(单位) | Rev.(版本) | Dimension Limit(尺寸范围) | Tolerance(公差) |
|--------------|----------|----------|-----------------------|---------------|
| V18-361605CF | mm       | Rev.4.0  | 0 ~ 10                | ±0.5          |
|              |          |          | 10 ~ 100              | ±1.0          |
|              |          |          | 100 ~ 150             | ±1.5          |
|              |          |          | 150 ~ 250             | ±2.0          |

