



1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树



Specifications

Rating: DC 12V/50mA


Contact Resistance: 500mΩ max

Insulation resistance: DC100V 60S 100MΩ min


Dielectric strength: AC250V(50~60HZ)60S min

Operating Life: 300,000cycles 100,00cycles

Travels: 0.13±0.05mm



RECOMMENDED P.C.B. LAYOUT



CIRCUIT DIAGRAM

PAPT NO	TS-2630-B
Operating Force	B:160gf C:260gf
Height	H:0.65

⑤	Knob	1	Polyamide	Black
④	Film	1	Polyamide	White
③	Dome	2	Stainless steel	Ag-Plated
②	Housing	1	Brass	Black
①	Terminal	1	PhosphoR Bronze	Ag-Plated
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	TACT SWITCH
APPROVED		SIZE: A4	PART NO.: TS-2630-B
			DWG NO.: TS-2630-B
SCALE	N/A	PAGE	1/1
		REVISION	A1