


SPECIFICATION

Physical Dimensions(尺寸图):

Unit(单位):mm



Item(项目)	Dimension(尺寸)	Tolerance(公差范围)	Unit(单位)
A	20.00	±0.40	mm
B	9.90	±0.20	mm
C	5.65	±0.25	mm
D	5.70	±0.20	mm
E	14.10	Min	mm
F	7.30	±0.30	mm

Electrical requirements(电气特性):

AL=1700±25% nH/N²

Electrical requirements(电气特性):

Testing Equipment(测试仪器): TH2775B OR EQU

Test frequency range(测试频率区间): 1KHz 0.3V

Test lead set(测试线组): 10Ts

Model.(型号)	Unit(单位)	Rev.(版本)	Dimension Limit(尺寸范围)	Tolerance(公差)
EF20-JP4	mm	Rev.4.0	0 ~ 10	±0.5
			10 ~ 100	±1.0
			100 ~ 150	±1.5
			150 ~ 250	±2.0

