

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 100V AC, DC.
4. 接触电阻: $\leq 0.04\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。
6. 额定电流: 1A AC, DC.

序号	品名	材质
①	1.5 Pitch A型 电池座胶芯	LCP UL94 V-0, 颜色: 黑色
②	1.5 Pitch A型 电池座端子	铜合金/表面镀锡
③	1.5 Pitch A型 电池座焊片	铜合金/表面镀锡

Part No	CKT	A	B	C
WAFER-PE1.5-2PWB-B4C	2	1.50	5.04	3.25
WAFER-PE1.5-3PWB-B4C	3	3.00	6.54	4.75
WAFER-PE1.5-4PWB-B4C	4	4.50	8.04	6.25
WAFER-PE1.5-5PWB-B4C	5	6.00	9.54	7.75
WAFER-PE1.5-6PWB-B4C	6	7.50	11.04	9.25
WAFER-PE1.5-7PWB-B4C	7	9.00	12.54	10.75
WAFER-PE1.5-8PWB-B4C	8	10.50	14.04	12.25
WAFER-PE1.5-9PWB-B4C	9	12.00	15.54	13.75
WAFER-PE1.5-10PWB-B4C	10	13.50	17.04	15.25
WAFER-PE1.5-11PWB-B4C	11	15.00	18.54	16.75
WAFER-PE1.5-12PWB-B4C	12	16.50	20.04	18.25
WAFER-PE1.5-13PWB-B4C	13	18.00	21.54	19.75
WAFER-PE1.5-14PWB-B4C	14	19.50	23.04	21.25
WAFER-PE1.5-15PWB-B4C	15	21.00	24.54	22.75
WAFER-PE1.5-16PWB-B4C	16	22.50	26.04	24.25

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.50 Pitch A型卧式电池座	
DECIMALS:	ANGLES:	PAR	WAFER-PE1.5-NPWB-B4C
X.: ± 0.50	$\pm 1^{\circ}$	DWN	Lucas
X.X: ± 0.20		CHKD	Ethan
X.XX: ± 0.10		APVD	Jacob
		SCALE: 1:1	UNIT: MM
		CUSTOMER COPY	SIZE: A4
			SHEET: 1F1
			REV: A



PAR	WAFER-PE1.5-NPWB-B4C
DWN	Lucas
CHKD	Ethan
APVD	Jacob
SCALE: 1:1	UNIT: MM
CUSTOMER COPY	SIZE: A4
	SHEET: 1F1
	REV: A

