


STRADDLE MOUNT WITH MOUNTING EAR TYPE



DIMENSIONS					
POSITION	A±0.20	B±0.15	C±0.20	D±0.25	E±0.30
36	6	7.65	12.30	25.00	34.8
64	20	21.65	26.30	39.00	48.8
98	37	38.65	43.30	56.00	65.8
164	70	71.65	76.30	89.00	98.8

NOTES 注释:

1. MATERIAL 材料:



1.1 HOUSING 外壳: THERMOPLASTIC, HIGH TEMP., UL94V-0;
COLOR: BLACK.

1.2 CONTACTS 触点: COPPER ALLOY.



2. FINISH 饰面:

2.1 CONTACT 触点:


SELECTEIVE GOLD PLATING ON CONTACT AREA.
100µ"MIN. MATTE TIN PLATING ON SOLDER TAILS,
50µ" MIN. NICKEL UNDERPLATING OVERALL.




								DSND		SCALE: N/A	MODEL TYPE:				
Δx					ANGLAR	±5°		DWN		VIEW: 	PART NO.:				
Δx					L ≤ 4	±0.2		CHKD		UNIT: mm/in	X3126WS-98-9TV01				
Δx					4<L ≤ 16	±0.3					DWG NO.:				
MARK	DESCRIPTION			DATE	REVISED	APPROVED		16<L ≤ 63	±0.4	X-X3126WS-98-9TV01					
							APPD		SIZE: A4						
							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														1/1	A0



RECOMMENDED OF PCB DIMENSIONS TOLERANCE: ±0.05



SCALE 2:1



DIMENSIONS				
POSITION	A	C	F	G
36	6	12.30	8.15	B PIN#17
64	20	26.30	22.15	B PIN#31
98	37	43.30	39.15	B PIN#48
164	70	76.30	72.15	B PIN#81


X3126 W S - 98 - 9T V01

① ② ③ ④ ⑤ ⑥




- ① Series Nunber
- ② Terminal form: W-Wafer
- ③ Welding Board Angle : Straddle
- ④ No.of Pins: 36~164 Pin
- ⑤ Plastic material: PA9T/PA46 UL94V-0
- ⑥ Contact Plating: V01-Gold Flash
V15-Gold 15u"
V30-Gold 30u"

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X3126WS-98-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X3126WS-98-9TV01
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0
XKB INDUSTRIAL PRECISION CO.,LIMITED			



E



DIMENSIONS	
POSITION	H
36	20.4
64	34.4
98	51.4
164	84.4

								DSND		SCALE: N/A	MODEL TYPE:			
					ANGULAR	±5°		DWN		VIEW: 	PART NO.:			
Δx					L≤ 4	±0.2		CHKD		UNIT: mm/in	X3126WS-98-9TV01			
Δx					4<L≤ 16	±0.3					DWG NO.:			
Δx					16<L≤ 63	±0.4					X-X3126WS-98-9TV01			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5		APPD		SIZE: A4				
REVISIONS								UNSPECIFIED TOLERANCES				XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn												WEIGHT	SHEET	REVISION
													1/1	A0