


SPECIFICATION

Physical Dimensions(尺寸图):

Unit(单位):mm



Item(项目)	Dimension(尺寸)	Tolerance(公差范围)	Unit(单位)
A	31.0	±0.8	mm
B	50.0	±2.0	mm
C	19.0	±0.5	mm

Electrical requirements(电气特性):

Z1=115 Ω Min at 25 MHz ;Z2=180 Ω Min at 100 MHz

Electrical requirements(电气特性):

Testing Equipment(测试仪器):E4991A

Test frequency range(测试频率区间):1-500MHz

Test lead set(测试线组):Ø0.5x0.5TSx165L(mm)

Model.(型号)	Unit(单位)	Rev.(版本)	Dimension Limit(尺寸范围)	Tolerance(公差)
VNCR-031050019-0F9	mm	Rev.4.0	0 ~ 10	±0.5
			10 ~ 100	±1.0
			100 ~ 150	±1.5
			150 ~ 250	±2.0

