

SPECIFICATION:

1.MATERIAL:

HOUSING:LCP UL 94V-0

COLOR:BLACK

CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:





CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS




30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL



ITEM	DIM A	形状	DIM B
SATA-09M-22BWB-C21	2.10		2.08
SATA-09M-22BWB-C23	2.30		

RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求			
3	Peg	Brass C2680R-H		Tin/Ni Plated	
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:SATA 7+15P 母座 SMT H:5.00 板上型
DECIMALS:	ANGLES:		PAR SATA-09M-22BWB-CN
.X:±0.30	.X':±3°		DWN Lucas
.XX:±0.20	.XX':±2°		CHKD Ethan
.XXX:±0.05	.XXX':±0.5°		APVD Jacob
CUSTOMER COPY			SCALE:1:1 UNIT:MM
			SIZE:A4 SHEET:1F1
			REV:A