

1.View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55~+150 ℃
3.IP Rating (防护级别)	IP 54
4.Diameter of socket end(插头端直径)	φ0.5
5.Testing Voltage (测试电压)	800V
6.Working Voltage (工作电压)	1200V
7.Rated Current (额定电流)	2.0A
8.Shell material(壳体材质)	Brass (chromium plating) shell and chuck nut/(nickel plating) pin sleeve and middleware/黄铜 (镀铬) 外壳和夹头螺母/ (镀镍) 插针套和中间件
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS


Sum up(总结)

Series(系列)	B
Shell style/model (外壳样式/型号)	TEG: Straight plug, cable collet, front seal and nut for fitting a bend relief (IP 54 when mate) 直塞、电缆夹头、前密封件和用于安装弯曲凸起 (配对时IP54)
Button (按键)	A button(一个按键)
Termination type (终止类型)	Male solder(公焊锡)
Line diameter awg(线材直径)	34~28AWG
Cable diameterφ (电缆直径)	φ6.3-7.2MM
Matching parts(配件)	ZGG.1B.P14.CLL

Location pin combination (定位销组合)

(编号) Number	Number of positioning pins(定 位销数量)	Angle(角度)	Series(系列)~1B
G	One(1)	A	(Zero degrees)0°
A	Two(2)		Thirty degrees(30°)
B	Two(2)		Sixty degrees(60°)
C	Two(2)		Ninety degrees(90°)
D	Two(2)	β	135 degrees(135°)
E	Two(2)		145 degrees(145°)
F	Two(2)		155 degrees(155°)
J	Two(2)	γ	Forty-five degrees(45°)
K	Two(2)		Seventy degrees(70°)
L	Two(2)		80 degrees(80°)


	A	B	C/V	ANGLE	
5-10	±0.02	±0.05	±0.1	0°-30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°-90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100~	±0.15%	±0.20%	±0.25%		



	A	L	M	S1	S2
MM	φ13.5	42	33	10.0	9
in	0.5315	1.6535	1.2992	0.3937	0.3543



Welded surface
(焊接面)



Positive view
(正视图)



Solder core
(焊接型公胶芯)

TE G. 1B. P14.C L A D 72 H

Model(型号)

Positioning pin(定位销)

Series(系列)

Needle core configuration(针芯配置)

Outer casing(外壳)

Insulator(绝缘体)

Needle core(针芯)

Type of clamp(线夹类型)

Cable diameter(电缆直径)

SH means a sheath type, not a cover type.

(H表示护套型，不表示为不带护套型)

DESIGNED (设计)		DATE(日期)		SCALE(比例)	NA/(不适用)	MODEL TYPE 型号类型: TEG. 1B P14. CLAD 72H
CHECKED (校对)		DATE(日期)		VIEW(视图)		PART NO. 1B14-core plug
APPROVED (审核)		DATE(日期)		UNIT(单位)	MM	名称: 1B14芯插头
REVISIONS				MATERIAL (材料)		DWG NO.:
www.helloxb.com www.helloxb.cn				XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT(重量) SHEET(张) REVISION(修订)
						1/1 A0