

SPECIFICATION:

1.MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA


100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDER TAILS

30u" NICKEL UNDERPLATING OVER ALL

ITEM	DIM A	形状	DIM B
SATA-10M-22AWB-C21	2.10		2.08
SATA-10M-22AWB-C23	2.30		

RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

环保要求		产品必须符合ROHS要求			
3	Peg	Brass C2680R-H		Tin/Ni Plated	
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:SATA 7+15P 母座 SMT H:5.00 板下型侧插式	
DECIMALS:	ANGLES:	PAR	SATA-10M-22AWB-CN
.X:±0.30	.X':±3°	DWN	Lucas
.XX:±0.20	.XX':±2°	CHKD	Ethan
.XXX:±0.05	.XXX':±0.5°	APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A