


SPECIFICATION

Physical Dimensions(尺寸图):

Unit(单位):mm



Item(项目)	Dimension(尺寸)	Tolerance(公差范围)	Unit(单位)
A	33.5	±1.2	mm
B	6.5	±0.5	mm
C	27.0	±0.7	mm
D	20.0	±0.7	mm
E	1.8	±0.5	mm

Electrical requirements(电气特性):

Z1=40 Ω Min at 25 MHz ;Z2=100 Ω Min at 100 MHz

Electrical requirements(电气特性):

Testing Equipment(测试仪器) :E4991A + 16194A

Test frequency range(测试频率区间) :1-500MHz

Test lead set(测试线组):Ø0.5x0.5TSx100L(mm)

Model.(型号)	Unit(单位)	Rev.(版本)	Dimension Limit(尺寸范围)	Tolerance(公差)
VNC-033006020-VN09-27x1.8	mm	Rev.4.0	0 ~ 10	±0.5
			10 ~ 100	±1.0
			100 ~ 150	±1.5
			150 ~ 250	±2.0

