




Surface Mount Ultra Fast Recovery Rectifier

Features

- Top-side Cooling(TSC) Packaging technology
- Compact and Slim Packaging Solutions
- For surface mounted applications
- Fast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

Mechanical Data

- Case: SMHM
- Terminals: leads solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end



Ordering Information

Part Number	Shipping	Reel
LTU3AM THRU LTU3MM	15000PCS Tape&Reel	13 inchs

Absolute Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	Symbol	LTU3AM	LTU3BM	LTU3DM	LTU3GM	LTU3JM	LTU3KM	LTU3MM	Unit
	Marking	U3A	U3B	U3D	U3G	U3J	U3K	U3M	
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current	I _{F(AV)}	3							A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	100							A
Maximum instantaneous forward voltage at 3.0A	V _F	1.0			1.3	1.65			V
Maximum DC reverse current T _A =25°C at rated DC reverse voltage T _A =100°C	I _R	1 100							µA
Typical junction capacitance (Note1)	C _j	50				30			pF
Maximum reverse recovery time (Note2)	t _{rr}	50				75			ns
Typical thermal resistance (Note3)	R _{θJA} R _{θJC}	38 6							°C/W
Operating and StorageTemperature Range	T _j , T _{stg}	-55 to +150							°C

Note: (1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(2) Measured with $I_F = 0.5 A$, $I_R = 1 A$, $t_{rr} = 0.25 A$.

(3) P.C.B. mounted with 0.08" × 0.08" (2mm × 2mm) copper pad areas.



Characteristics Curves

FIG. 1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS







FIG. 5 TYPICAL JUNCTION CAPACITANCE



Package Outline
SMHM
Unit : mm


UNIT		A	C	D	E	H _E	d	e	f	h	∠
mm	max	0.99	0.25	3.60	3.00	4.30	2.10	2.10	2.00	0.70	6°
	min	0.83	0.15	3.20	2.60	3.70	1.90	1.90	1.78	0.50	


Suggested Pad Layout
SMHM
Unit : mm


Note:

1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.05 mm.
3. The pad layout is for reference purpose only.

Carrier Tape Dimensions

Unit : mm





Symbol	Spec	Symbol	Spec
W	12.0±0.10	P2	2.00±0.10
E	1.75±0.10	t	0.25±0.03
F	5.50±0.10	t1	0.05+
D0	1.55±0.10	A0	3.05±0.10
D1	1.50±0.10	B0	4.15±0.10
P0	4.00±0.10	K0	1.15±0.10
P1	4.00±0.10		

Reel Dimensions

Unit : mm

13" Reel




D5	Φ330.0±5.0
D6	Φ13.5±0.5
H	2.5±1.0
W2	12±2.0

Quantity: 15000PCS


Packaging



15000 PCS/Reel



5 Reel/Inner Box
75 KPCS/Inner Box



Dim(Unit:mm)
340mm*340mm*85mm

Dim(Unit:mm)
360mm*360mm*355mm




4 Boxes per carton
300 KPCS per carton

13 inches Reel



Recommended Soldering Conditions



Important Notice and Disclaimer

Leading-Tech reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Leading-Tech makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Leading-Tech assume any liability for application assistance or customer product design.

Leading-Tech does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Leading-Tech.

Leading-Tech products are not authorized for use as critical components in life support devices or systems without express written approval of Leading-Tech.

Version Update Information

Series NO.	Enactment/Revision Date	Effective Date	Version	Revision Content	Revision Reason	Revision Person	Note
01	2025.12.09	2025.12.09	1.0	New file	/	Ding	