


Surface Mount Schottky Barrier Rectifier

Features

- Top-side Cooling(TSC) Packaging technology
- Compact and Slim Packaging Solutions
- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- Meets MSL level 1, per J-STD-020
- Lead free in comply with EU RoHS 2011/65/EU directives



Mechanical Data

- Case:SMHL
- Terminals: leads solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end

Ordering Information

Part Number	Shipping	Reel
LT52HL THRU LT520HL	7500PCS Tape&Reel	13 inches

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	Symbol	LT52HL	LT54HL	LT56HL	LT510HL	LT520HL	Unit
	Marking	S52	S54	S56	S510	S520	
Maximum repetitive peak reverse voltage	V _{RRM}	20	40	60	100	200	V
Maximum RMS voltage	V _{RMS}	14	28	42	70	140	V
Maximum DC blocking voltage	V _{DC}	20	40	60	100	200	V
Maximum average forward rectified current at T _L (see fig.1)	I _(AV)	5.0					A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	120.0					A
Maximum instantaneous forward voltage at 5.0A	V _F	0.55		0.65	0.80	0.85	v
Maximum DC reverse current T _A =25℃ at rated DC blocking voltage T _A =100℃	I _R	20			2		uA
		5			3		mA
Typical junction capacitance (Note1)	C _J	500			300		pF
Typical thermal resistance (Note2)	R _{θJA}	48					℃/W
	R _{θJC}	4					
Operating junction temperature range	T _J	-55 to +125					℃
Storage temperature range	T _{STG}	-55 to +125					℃

Note: (1) Measured at 1MHz and applied reverse voltage of 4.0V D.C.

(2) PCB mounted with 0.2"x0.2"(5mmx5mm) copper pad areas.



Characteristics Curves

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance






Fig.5 Maximum Non-Repetitive Peak Forward Surge Current



Package Outline

SMHL

Unit : mm




UNIT		A	C	D	E	H _E	d	e	f	h	∠
mm	max	1.00	0.25	4.60	3.80	5.30	2.90	2.90	2.95	0.60	6°
	min	0.90	0.15	4.20	3.40	4.70	2.70	2.70	2.75	0.40	

Suggested Pad Layout

SMHL

Unit : mm




Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purpose only.

Carrier Tape Dimensions

Unit : mm





Symbol	Spec	Symbol	Spec
W	12.0±0.10	P2	2.00±0.10
E	1.75±0.10	t	0.25±0.03
F	5.50±0.10	t1	0.05+
D0	1.55±0.10	A0	3.05±0.10
D1	1.50±0.10	B0	4.15±0.10
P0	4.00±0.10	K0	1.15±0.10
P1	4.00±0.10		

Reel Dimensions

Unit : mm

13" Reel




D5	Φ330.0±5.0
D6	Φ13.5±0.5
H	2.5±1.0
W2	12±2.0

Quantity: 7500PCS


Packaging



7500PCS/Reel



5Reel/Inner Box
37.5KPCS/Inner Box



Dim(Unit:mm)
340mm*340mm*85mm

Dim(Unit:mm)
360mm*360mm*355mm




4 Boxes per carton
150KPCS per carton

13 inches Reel



Recommended Soldering Conditons



Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3°C/second max.
Preheat	
-Temperature Min ($T_{S\ min}$)	150°C
-Temperature Max ($T_{S\ max}$)	200°C
-Time (min to max) (t_s)	60-180 seconds
$T_{S\ max}$ to T_L	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
-Temperature (T_L)	217°C
-Time (t_L)	60-150 seconds
Peak Temperature (T_P)	260°C
Time within 5°C of actual Peak Temperature (t_p)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

Important Notice and Disclaimer

Leading-Tech reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Leading-Tech makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Leading-Tech assume any liability for application assistance or customer product design.

Leading-Tech does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Leading-Tech.

Leading-Tech products are not authorized for use as critical components in life support devices or systems without express written approval of Leading-Tech.

Version Update Information

Series NO.	Enactment/Revision Date	Effective Date	Version	Revision Content	Revision Reason	Revision Person	Note
01	2025.09.27	2025.09.27	1.0	New file	/	Ding	