

Features

- * Ultra low leakage: nA level
- * Low clamping voltage
- * RoHS Compliant
- * REACH & SVHC Compliant
- * Halogen Compliant
- * SOD-523 Package




SOD-523

Ordering Information


Part Number	Packaging	Marking
FSJEB05D5	3000/Tape & Reel	5B

Circuit Diagram



Portion Electronics Parameter

Symbol	Parameter
V_{RWM}	Peak Reverse Working Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}




Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs pulse)	P_{pk}	100	W
Peak Pulse Current (8/20 μs pulse)	I_{PP}	8	A
ESD per IEC 61000-4-2 (Air)	V_{ESD}	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	T_J	-40 to +125	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 to +150	$^{\circ}\text{C}$


Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				5	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	5.5		7.5	V
Reverse Leakage Current	I_R	$V_{RWM} = 5\text{V}$			100	nA
Clamping Voltage	V_C	$I_{PP} = 1\text{A}$ (8 / 20 μs pulse)		7.0	9	V
Clamping Voltage	V_C	$I_{PP} = 8\text{A}$ (8 / 20 μs pulse)		8.2	13	V
Junction Capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$,		15	20	pF


Typical Performance Characteristics ($T_A=25^\circ\text{C}$ unless otherwise Specified)



8 / 20us Pulse Waveform




IEC61000-4-2 Pulse Waveform




Power Derating Curve

SOD-523 Package Outline Drawing



SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	Min	Typ	Max	Min	Typ	Max
A	0.60	0.65	0.70	0.0236	0.0256	0.0276
B	1.15	1.20	1.25	0.0453	0.0472	0.0492
B1	1.55	1.60	1.65	0.0610	0.0630	0.0650
C	0.75	0.80	0.85	0.0295	0.0315	0.0335
D	0.10	0.11	0.12	0.0039	0.0043	0.0047
D1	0.28	0.30	0.32	0.0110	0.0118	0.0126
E	0.00	-	0.02	0.0000	-	0.0008

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETER	INCHES
X1	2.00	0.079
X2	0.60	0.024
X3	0.80	0.031
Y1	0.50	0.020