








REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
1	NEW			jimmy	2015/1/16
2	Original Model: U522-2			HUABO	2023/10/17



RECOMMENDED P.C.B LAYOUT
COMPONENT SIDE(TOLERANCE ±0.05)



TECHNICAL CHARACTERISTICS

1.General Characteristics

Durability:10,000 cycles min.

2.Electrical Characteristics

Current rating: (1&5Pin)1.8A;
(2&3&4Pin)0.5A Max.

Contact resistance:Initial: 40mΩ Max.
After Test: 50mΩ Max.

Insulation resistance:>1000MΩ/250V DC

3.Solderability

IR reflow: 250°C,5sec.Max

Manual soldering: 370°C,3sec.Max

4.Environmental Characteristics

Operating temperature: -40°C~+85°C

Operating humidity:10%~+95%RH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	BASE	1	LCP	Black UL94V-0
2	SHELL	1	STAINLESS STEEL	Ni plated over all
3	DATA CONTACT	5	Copper Alloy	Contact area:Gold plated

Unless otherwise
specified, other
tolerance are:

MUP MUP INDUSTRIAL CO.,LTD.

X	±0.35	X*	±5°
X.X	±0.25	X.X*	±4°
X.XX	±0.15	X.XX*	±3°
X.XXX	±0.10	X.XXX*	±2°

NAME: **Micro USB Connector**

MODEL NO: **MUP-U5022-02**

TYPE: **Without post DIPx4**

PROJ.	UNIT	SCALE
⊕	MM	1:1

DRAWN	Jimmy 2015/01/16
CHECKED	Zoey 2015/01/16
APPROVAL	Simon 2015/01/16

DWG NO.:	DWG-U5022-02-03
SHEET	1/1
REVISION	2



CUSTOMER DRAWING